153C-D13JBD-D25-3-4R-6XP

440V/480V
3PH 50/60Hz
L1 L2 L3

CB1
L1 1L1
L2 1L2
L3 1L3

SMC-3
L1/1 T1/2
L2/3 T2/4
L3/5 T3/6
SMC
SMC POWER TERMINALS (SEE MANUAL)

+REMOTE
MTR1
U1
V1
W1
PE
M
3 ~
GRD

L1 BLK L2 BLK
TB1 L1 TB1 L2

PLUG K
L1 L2
L1 L2
FU1 FU2
H1 H4
H1 H4
H2 H3
TR1
X1 X2
GRD

SMC A1 QC L
QC LT LT FU3 X1
N QC N

HAND/OFF/AUTO
QC L L 13 14 4
QC 4
SR A1 A2
QC 3 11 SR 14
23 24 5
QC 5 +REMOTE QC 4
ON PL2 P1 X1 R X2 N
QC N
PLUG E
PLUG B

SR 21 24
SMC IN1
SMC IN2

SMC 97 98 QC F

SR 21 22 QC P2

QC N SMC A2

SMC A1
L RED
FAN 1 2 3 4
N WHT

NOTES:

1. USE 75ºC CU WIRE ONLY
2. LINE FUSES SUPPLIED BY CUSTOMER WHEN DISCONNECT SWITCH IS SUPPLIED. REFER TO NEC WHEN SELECTING SHORT CIRCUIT PROTECTION
3. ADDITIONAL CONTROL CIRCUIT OVERCURRENT PROTECTION REQUIRED FOR NON-COMBINATION STARTERS. REFER TO NATIONAL ELECTRIC CODE.
4. DIP SWITCH DEFAULT FACTORY SETTINGS

1= O	9= O
2= I	10= O
3= O	11= I
4= O	12= O
5= I	13= O
6= O	14= O
7= O	15= I
8= O	16= O

Wire Connector Torque	
Line Terminal (Lb.In.)	Load Terminal (Lb.In.)
88	200

Rockwell Automation

CONFIDENTIAL AND PROPRIETARY INFORMATION:
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION OF ROCKWELL AUTOMATION, INC., AND MAY NOT BE USED, COPIED OR DISCLOSED TO OTHERS, EXCEPT WITH THE AUTHORIZED WRITTEN PERMISSION OF ROCKWELL AUTOMATION, INC.

Title: SMC COMBO

S.O.

CATALOG NO. 153C-D13JBD-D25-3-4R-6XP

Drawn by: AUTO_GEN | **Date:** 12/28/17 | **Sheet:** 1 of 2 | **Ver:** 00 | **Size:** D