



CATALOG NO.	FOR SIZE [mm]	L1	L2	W	X	Y	Z	N	SI DIN 912 SOCKET HEAD CAP SCREW	WEIGHT [kg]
LDAT-S03-HPBRKT	30	60	51.90	81	22	60	42.5	2	M6 X 1.0 X 14 LG	0.26
LDAT-S0507-HPBRKT	50/75	78	55.55	92	38	70	51.5	2	M6 X 1.0 X 14 LG	0.43
LDAT-S10-HPBRKT	100	93	49.20	135	45	100	61.5	2	M8 X 1.25 X 14 LG	0.91
LDAT-S15-HPBRKT	150	103	49.20	179	45	150	66.5	3	M8 X 1.25 X 14 LG	1.30

NOTE:  
 1. ALL DIMENSIONS ARE IN MILLIMETERS  
 2. TOLERANCES APPLY ONLY WHEN SPECIFIED  
 3. ASSEMBLY INCLUDES 1 PAYLOAD BRACKET,  
 AND 4 MOUNTING SCREWS

**Rockwell  
Automation**

LDAT, PAYLOAD BRACKET KIT, ESM

Drawn by: JAL

Date: 05-22-12

CONFIDENTIAL AND PROPRIETARY INFORMATION.  
 THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY  
 INFORMATION OF ROCKWELL AUTOMATION, INC. AND MAY  
 NOT BE USED, COPIED OR DISCLOSED TO OTHERS, EXCEPT  
 WITH THE AUTHORIZED WRITTEN PERMISSION OF ROCKWELL  
 AUTOMATION, INC.

Sheet 1 Of 1

Size	Ver
<b>B</b>	<b>00</b>

**10000285044**