




NOTES:
1. ENCLOSURE SYSTEM IS 2000MM AND 600MM DEEP
2. PLEASE CHECK rockwellautomation.literature.com FOR ADDITIONAL INFORMATION ON THE POWERFLEX 755T DRIVES.

2. DRIVE SIZE SHOWN:	INPUT VOLTAGE	NORMAL DUTY RATING
	400	2920 kW
	480	4800 HP
	600	4100 HP
	690	3650 kW

DIMENSIONS IN MM
UNLESS OTHERWISE SPECIFIED
DIMENSIONS & TOLERANCING IN ACCORDANCE WITH ASME Y14.5-2009
ALL UNTOLERANCED DIMENSIONS ARE BASIC AND CONTROLLED BY THE CAD MODELS AND CONTROLLED SIMULTANEOUSLY

Rockwell Automation

PF755TR AFE DRIVES FRAME14
INLINE INSTALLATION SPECIFICATION

CONFIDENTIAL AND PROPRIETARY INFORMATION. THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION OF ROCKWELL AUTOMATION, INC. AND MAY NOT BE USED, COPIED OR DISCLOSED TO OTHERS, EXCEPT WITH THE AUTHORIZED WRITTEN PERMISSION OF ROCKWELL AUTOMATION, INC.

Sheet 1 Of 2

SIZE DIR
D 10003489179

VER
00

DRAWN BY: MLACHAW
DATE: 10-26-2017

