




- NOTES:
- ENCLOSURE SYSTEM IS 2000MM TALL AND 600MM DEEP.
 - PLEASE CHECK ROCKWELLAUTOMATION.LITERATURE.COM FOR ADDITIONAL INFORMATION ON THE POWERFLEX 755T DRIVES.
 - DRIVE SIZE SHOWN:

INPUT VOLTAGE	NORMAL DUTY RATING
400	3051 kW
480	3372 kW
600	3102 kW
690	3300 kW

DIMENSIONS IN MM
UNLESS OTHERWISE SPECIFIED
DIMENSIONS & TOLERANCING IN ACCORDANCE WITH ASME Y14.5-2009
ALL UNTOLERANCED DIMENSIONS ARE BASIC AND CONTROLLED BY THE CAD MODELS AND CONTROLLED SIMULTANEOUSLY

Rockwell Automation

PF750R,FR15,TM,BS,INLINE,INSTL
INLINE INSTALLATION SPECIFICATION

Drawn by: MLACHAW

CONFIDENTIAL AND PROPRIETARY INFORMATION. THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION OF ROCKWELL AUTOMATION, INC. AND MAY NOT BE USED, COPIED OR DISCLOSED TO OTHERS, EXCEPT WITH THE AUTHORIZED WRITTEN PERMISSION OF ROCKWELL AUTOMATION, INC.


Sheet 1 Of 2

Ver 00

D

10003548429

Date: NOV-17-2017



NOTES:
1. GROUND BUSBARS ARE 10MM THICK

DIMENSIONS IN MM
UNLESS OTHERWISE SPECIFIED
DIMENSIONS & TOLERANCING IN ACCORDANCE
WITH ASME Y14.5-2009
ALL UNTOLERANCED DIMENSIONS ARE BASIC
AND CONTROLLED BY THE CAD MODELS AND
CONTROLLED SIMULTANEOUSLY

Rockwell Automation		CONFIDENTIAL AND PROPRIETARY INFORMATION. THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION OF ROCKWELL AUTOMATION, INC. AND MAY NOT BE USED, COPIED OR DISCLOSED TO OTHERS, EXCEPT WITH THE AUTHORIZED WRITTEN PERMISSION OF ROCKWELL AUTOMATION, INC.	
PF750R,FR15,TM,BS,INLINE,INSTL INLINE INSTALLATION SPECIFICATION		Sheet 2 Of 2	
Size D	10003548429	Ver	00
Drawn by: MLACHAW		Date: NOV-17-2017	