

Bulletin 1492
Screw Connection Terminal Blocks
 Isolation Blocks

	1492-JKD3			1492-JKD3TP			1492-H7		
Dimensions are not intended to be used for manufacturing purposes. Note: Height dimension is measured from top of rail to top of terminal block.									
Specifications	<i>Knife Disconnect Feed-Through Terminal Block</i>			<i>Knife Disconnect Feed-Through Terminal Block with test plug socket</i>			<i>Handle-Style Isolating Terminal Block.</i>		
Certifications									
Voltage Rating	600V AC/DC		500V AC/DC	600V AC/DC		500V AC/DC	300V AC/DC	300V AC/DC	500V AC/DC
Maximum Current	20 A		24 A	20 A		24 A	15 A		15 A
Wire Range (Rated Cross Section)	30... 12 AWG		2.5 mm ²	30... 12 AWG		2.5 mm ²	#30... #12 AWG	0.05... 4.0 mm ²	
Fuse Size (Dummy Fuse Supplied)	—			—			1/4 in x 1-1/4 in		
Wire Strip Length	0.39 in (10 mm)			0.39 in (10 mm)			0.38 in (9.7 mm)		
Recommended Tightening Torque	3.5...7.1 lb•in (0.4...0.8 Nm)			4.4...5.3 lb•in (0.5...0.6 Nm)			3...7 lb•in (0.3...0.8 Nm)		
Density (Blocks per ft/meter)	49 per ft/163 per meter			49 per ft/163 per meter			33 pcs/ft (109/m)		
Housing Temperature Range	-58...+248 °F (-50...+120 °C)			-58...+248 °F (-50...+120 °C)			-40...+221 °F (-40...+105 °C)		
Terminal Blocks	Cat. No.	Pcs/Pkg	Cat. No.	Pcs/Pkg	Cat. No.	Pcs/Pkg	Cat. No.	Pcs/Pkg	Cat. No.
Color:	Gray	1492-JKD3	50	1492-JKD3TP	50	1492-H7	—	—	—
	Black	—	—	—	—	—	1492-H7	25	—
Accessories	Cat. No.	Pcs/Pkg	Cat. No.	Pcs/Pkg	Cat. No.	Pcs/Pkg	Cat. No.	Pcs/Pkg	Cat. No.
Mounting Rails:									
3 ft Scored A-B Rail	—	—	—	—	1492-N1	20			
3 ft Rigid A-B Rail	—	—	—	—	1492-N22	20			
3 ft Rigid Rise A-B Rail	—	—	—	—	1492-N44	2			
Standoff Brackets (use every 12 in)	—	—	—	—	1492-N25	2			
1 m Symmetrical DIN (Steel)	199-DR1	10	199-DR1	10	199-DR1	10			
1 m Symmetrical DIN (Aluminum)	1492-DR5	10	1492-DR5	10	1492-DR5	10			
1 m Hi-Rise Sym. DIN (Aluminum)	1492-DR6	2	1492-DR6	2	1492-DR6	2			
1 m Angled Hi-Rise Sym. DIN (Steel)	1492-DR7	2	1492-DR7	2	1492-DR7	2			
End Barriers	1492-EBJ3	50	1492-EBJ3	50	1492-N37	50			
End Anchors and Retainers:									
A-B Rail — Heavy Duty	—	—	—	—	1492-N23	10			
A-B Rail — Normal Duty	—	—	—	—	1492-N47	50			
Screwless End Retainer	1492-ERL35	20	1492-ERL35	20	1492-ERL35	20			
DIN Rail — Normal Duty	1492-EAJ35	100	1492-EAJ35	100	1492-EAJ35	100			
DIN Rail — Heavy Duty	1492-EAHJ35	50	1492-EAHJ35	50	1492-EAHJ35	50			
Jumpers:									
Screw Center Jumper — 50 Pole	1492-CJLJ5-50	10	1492-CJLJ5-50	10	—	—			
Screw Center Jumper — 10 Pole	1492-CJLJ5-10	20	1492-CJLJ5-10	20	—	—			
Screw Center Jumper — 9 Pole	1492-CJLJ5-9	20	1492-CJLJ5-9	20	—	—			
Screw Center Jumper — 8 Pole	1492-CJLJ5-8	20	1492-CJLJ5-8	20	—	—			
Screw Center Jumper — 7 Pole	1492-CJLJ5-7	20	1492-CJLJ5-7	20	—	—			
Screw Center Jumper — 6 Pole	1492-CJLJ5-6	20	1492-CJLJ5-6	20	—	—			
Screw Center Jumper — 5 Pole	1492-CJLJ5-5	20	1492-CJLJ5-5	20	—	—			
Screw Center Jumper — 4 Pole	1492-CJLJ5-4	60	1492-CJLJ5-4	60	—	—			
Screw Center Jumper — 3 Pole	1492-CJLJ5-3	60	1492-CJLJ5-3	60	—	—			
Screw Center Jumper — 2 Pole	1492-CJLJ5-2	60	1492-CJLJ5-2	60	—	—			
Insulated Side Jumper — 24 Pole	1492-SJ5B-24	50	1492-SJ5B-24	50	—	—			
Insulated Side Jumper — 10 Pole	1492-SJ5B-10	50	1492-SJ5B-10	50	—	—			
Uninsulated Side Jumper — 10 Pole	—	—	—	—	1492-N49	10			
Side Jumper — Insulating Sleeve	—	—	—	—	1492-SJS	10			
Screw Type Jumper Notching Tool	1492-T1	1	1492-T1	1	—	—			
Other Accessories:									
Partition Plate	1492-EBJ16	20	1492-EBJ16	20	—	—			
Test Plug	—	—	1492-TP23	20	—	—			
Group Marking Carrier	1492-GM35	25	1492-GM35	25	1492-GM35	25			
Marking Systems:									
Snap-in marker cards	1492-M5X12 (144/card)	5	1492-M5X12 (144/card)	5	1492-MS8X12 (56/card)	5			
Snap-in marker cards	1492-M5X5 (200/card)	5	1492-M5X5 (200/card)	5	1492-MS8X9 (56/card)	5			
Adhesive Labels	—	—	—	—	1492-ALHFB (50/sheet)	1			