

# Spring Clamp Connection Terminal Blocks

Mini-Block, 600V UL Rated, Interlocking

	1492-LM3			1492-LM3Q			1492-LMG3			
<p>Dimensions are not intended to be used for manufacturing purposes.                      Note: Height dimension is measured from top of rail to top of terminal block.</p>										
	<b>Specifications</b>	<i>Mini rail-mount, Feed-through Terminal Block</i>			<i>Mini 4 point, rail-mount, Feed-through Terminal Block</i>			<i>Mini rail-mount grounding Terminal Block</i>		
	<b>Certifications</b>		<b>CSA</b>	<b>IEC</b>		<b>CSA</b>	<b>IEC</b>		<b>CSA</b>	<b>IEC</b>
	<b>Voltage Rating</b>	600V AC/DC			600V AC/DC			—		
<b>Maximum Current</b>	20 A	25 A	24 A	20 A	25 A	24 A	Grounding			
<b>Wire Range (Rated Cross Section)</b>	#26...12 AWG		2.5 mm <sup>2</sup>	#26...12 AWG		2.5 mm <sup>2</sup>	#26...12 AWG		2.5 mm <sup>2</sup>	
<b>Wire Strip Length</b>	0.39 in. (10 mm)			0.39 in. (10 mm)			0.39 in. (10 mm)			
<b>Density</b>	59 pcs/ft (196 pcs/m)			30 pcs/ft (99 pcs/m)			59 pcs/ft (196 pcs/m)			
<b>Housing Temperature Range</b>	-58...+248 °F (-50...+120 °C)			-58...+248 °F (-50...+120 °C)			-58...+248 °F (-50...+120 °C)			
<b>Terminal Blocks</b>		<b>Cat. No.</b>	<b>Pkg Qty.</b>		<b>Cat. No.</b>	<b>Pkg Qty.</b>		<b>Cat. No.</b>	<b>Pkg Qty.</b>	
<b>Color</b>	Grey	<b>1492-LM3</b>	100		<b>1492-LM3Q</b>	100		—	—	
	Blue	<b>1492-LM3-B</b>	100		<b>1492-LM3Q-B</b>	100		—	—	
	Green/Yellow	—	—		—	—		<b>1492-LMG3</b>	100	
<b>Accessories</b>		<b>Cat. No.</b>	<b>Pkg Qty.</b>		<b>Cat. No.</b>	<b>Pkg Qty.</b>		<b>Cat. No.</b>	<b>Pkg Qty.</b>	
<b>Mounting Rails</b>										
1 m Symmetrical Mini DIN (Steel)		<b>1492-DR3</b>	5		<b>1492-DR3</b>	5		<b>1492-DR3</b>	5	
<b>Screwless End Retainer</b>	Grey	<b>1492-ERL15</b>	20		<b>1492-ERL15</b>	20		<b>1492-ERL15</b>	20	
<b>End Anchor</b>	Grey	<b>1492-EAJ15</b>	50		<b>1492-EAJ15</b>	50		<b>1492-EAJ15</b>	50	
<b>Jumpers</b>										
Side Jumper — 2-Pole		<b>1492-SJLM5-2</b>	50		<b>1492-SJLM5-2</b>	50		—	—	
Side Jumper Installation Tool		<b>1492-TAL5-2</b>	1		<b>1492-TAL5-2</b>	1		—	—	
<b>End Barriers</b>	Grey	<b>1492-EBLM3</b>	50		<b>1492-EBLM3</b>	50		<b>1492-EBLM3</b>	50	
	Blue	<b>1492-EBLM3-B</b>	50		<b>1492-EBLM3-B</b>	50		<b>1492-EBLM3-B</b>	50	
	Yellow	<b>1492-EBLM3-Y</b>	50		<b>1492-EBLM3-Y</b>	50		<b>1492-EBLM3-Y</b>	50	
<b>Marking Systems</b>										
Snap-In Marker Cards		<b>1492-M5X10</b> (144/card)	5		<b>1492-M5X10</b> (144/card)	5		<b>1492-M5X10</b> (144/card)	5	
Snap-In Marker Cards		<b>1492-M5X5</b> (200/card)	5		<b>1492-M5X5</b> (200/card)	5		<b>1492-M5X5</b> (200/card)	5	
Hinged Marker Cards		<b>1492-MH5X10</b> (96/card)	5		<b>1492-MH5X10</b> (96/card)	5		<b>1492-MH5X10</b> (96/card)	5	