

Screw Connection Terminal Blocks

Plug-In Style Terminal Blocks

	1492-JD3PTP			1492-JD3PSS			1492-JD3PSSTP		
Dimensions are not intended to be used for manufacturing purposes. Note: Height dimension is measured from top of rail to top of terminal block.									
Specifications	Two-circuit selectable component plug-in terminal block with test plug socket			Two-circuit selectable component plug-in terminal block with internal surge suppressor			Two-circuit selectable component plug-in terminal block with internal surge suppressor and test plug socket		
Certifications		CSA	IEC		CSA	IEC		CSA	IEC
Voltage Rating	300V AC/DC			300V AC/DC			115V AC		
Maximum Current	20 A			20 A			24 A		
Wire Range (Rated Cross Section)	#24...12 AWG	#30...12 AWG	2.5 mm ²	#24...12 AWG	#30...12 AWG	2.5 mm ²	#24...12 AWG	#30...12 AWG	2.5 mm ²
Wire Strip Length	0.31 in. (8 mm)			0.31 in. (8 mm)			0.31 in. (8 mm)		
Recommended Tightening Torque	4.4 lb•in (0.5 N•m)			4.4 lb•in (0.5 N•m)			4.4 lb•in (0.5 N•m)		
Density	59 pcs/ft (196 pcs/m)			59 pcs/ft (196 pcs/m)			59 pcs/ft (196 pcs/m)		
Housing Temperature Range	-58...+248 °F (-50...+120 °C)			-58...+248 °F (-50...+120 °C)			-58...+248 °F (-50...+120 °C)		
Short-Circuit Current Rating	See page 12-42								
Terminal Blocks	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.	Cat. No.
Color: Grey	1492-JD3PTP	50	1492-JD3PSS	50	1492-JD3PSSTP	50			
Accessories	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.	Cat. No.
Mounting Rails:									
1 m Symmetrical DIN (Steel)	199-DR1	10	199-DR1	10	199-DR1	10			
1 m Symmetrical DIN (Aluminum)	1492-DR5	10	1492-DR5	10	1492-DR5	10			
1 m Hi-Rise Sym. DIN (Aluminum)	1492-DR6	2	1492-DR6	2	1492-DR6	2			
1 m Angled Hi-Rise Sym. DIN (Steel)	1492-DR7	2	1492-DR7	2	1492-DR7	2			
End Barriers	1492-EBJD3P	20	1492-EBJD3P	20	1492-EBJD3P	20			
End Anchors and Retainers:									
Screwless End Retainer	1492-ERL35	20	1492-ERL35	20	1492-ERL35	20			
DIN Rail — Normal Duty	1492-EAJ35	100	1492-EAJ35	100	1492-EAJ35	100			
DIN Rail — Heavy Duty	1492-EAHJ35	50	1492-EAHJ35	50	1492-EAHJ35	50			
Jumpers:									
Screw Center Jumper — 10-Pole	1492-CJJ5-10	20	1492-CJJ5-10	20	1492-CJJ5-10	20			
Screw Center Jumper — 4-Pole	1492-CJJ5-4	50	1492-CJJ5-4	50	1492-CJJ5-4	50			
Screw Center Jumper — 3-Pole	1492-CJJ5-3	50	1492-CJJ5-3	50	1492-CJJ5-3	50			
Screw Center Jumper — 2-Pole	1492-CJJ5-2	50	1492-CJJ5-2	50	1492-CJJ5-2	50			
Screw Type Jumper Notching Tool	1492-T1	1	1492-T1	1	1492-T1	1			
Other Accessories:									
Partition Plate	1492-PPJD3P	20	1492-PPJD3P	20	1492-PPJD3P	20			
Test Plug	1492-TP23	20	—	—	1492-TP23	20			
Disconnect Plug	1492-DPL	50	1492-DPL	50	1492-DPL	50			
Component Plug	1492-CPL	50	1492-CPL	50	1492-CPL	50			
Fuse Plug									
Without Blown Fuse Indicator	1492-FPK2	20	1492-FPK2	20	1492-FPK2	20			
10...36V Blown Fuse Indicator	1492-FPK224	20	1492-FPK224	20	1492-FPK224	20			
35...70V Blown Fuse Indicator	1492-FPK248	20	1492-FPK248	20	1492-FPK248	20			
60...150V Blown Fuse Indicator	1492-FPK2120	20	1492-FPK2120	20	1492-FPK2120	20			
140...250V Blown Fuse Indicator	1492-FPK2250	20	1492-FPK2250	20	1492-FPK2250	20			
Group Marking Carrier	1492-GM35	25	1492-GM35	25	1492-GM35	25			
Marking Systems:									
Snap-in marker cards	1492-SM5X10 (144/card)	5	1492-SM5X10 (144/card)	5	1492-SM5X10 (144/card)	5			
Snap-in marker cards	1492-M5X5 (200/card)	5	1492-M5X5 (200/card)	5	1492-M5X5 (200/card)	5			