

Screw Connection Terminal Blocks

Neutral Disconnect & Installation Blocks

	1492-JDG3ND			1492-JD3N			1492-JDG3N		
Dimensions are not intended to be used for manufacturing purposes. Note: Height dimension is measured from top of rail to top of terminal block.									
Specifications	3-Level terminal block with neutral disconnect and ground connection			2-Level feed-through terminal block for installation applications			3-Level terminal block with 2 feed-through and ground connection		
Certifications		CSA	IEC		CSA	IEC		CSA	IEC
Voltage Rating	300V AC/DC		400V AC/DC	300V AC/DC		400V AC/DC	300V AC/DC		400V AC/DC
Maximum Current	15 A	10 A	24 A	15 A	10 A	24 A	15 A	10 A	24 A
Wire Range (Rated Cross Section)	#22...12 AWG	#26...12 AWG	2.5 mm ²	#22...12 AWG	#26...12 AWG	2.5 mm ²	#22...12 AWG	#26...12 AWG	2.5 mm ²
Wire Strip Length	0.31 in. (8 mm)			0.31 in. (8 mm)			0.31 in. (8 mm)		
Recommended Tightening Torque	7.0 lb•in (0.8 N•m)			7.0 lb•in (0.8 N•m)			7.0 lb•in (0.8 N•m)		
Density	49 pcs/ft (163 pcs/m)			49 pcs/ft (163 pcs/m)			49 pcs/ft (163 pcs/m)		
Housing Temperature Range	-58...+248 °F (-50...+120 °C)			-58...+248 °F (-50...+120 °C)			-58...+248 °F (-50...+120 °C)		
Short-Circuit Current Rating	See page 12-42								
Terminal Blocks	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.	Cat. No.
Color: Grey	1492-JDG3ND	50	1492-JD3N	50	1492-JDG3N	50			
Accessories	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.	Cat. No.
Mounting Rails:									
1 m Symmetrical DIN (Steel)	199-DR1	10	199-DR1	10	199-DR1	10			
1 m Symmetrical DIN (Aluminum)	1492-DR5	10	1492-DR5	10	1492-DR5	10			
1 m Hi-Rise Sym. DIN (Aluminum)	1492-DR6	2	1492-DR6	2	1492-DR6	2			
1 m Angled Hi-Rise Sym. DIN (Steel)	1492-DR7	2	1492-DR7	2	1492-DR7	2			
End Barriers Grey	1492-BSPJLD3N	20	1492-BSPJLD3N	20	1492-BSPJLD3N	20			
Busbar Support Plates Blue	1492-BSPJLD3N-B	20	1492-BSPJLD3N-B	20	1492-BSPJLD3N-B	20			
End Anchors and Retainers:									
Screwless End Retainer	1492-ERL35	20	1492-ERL35	20	1492-ERL35	20			
End Anchor — Normal Duty	1492-EAJ35	100	1492-EAJ35	100	1492-EAJ35	100			
End Anchor — Heavy Duty	1492-EAHJ35	50	1492-EAHJ35	50	1492-EAHJ35	50			
Jumpers:									
Screw Center Jumper — 10-pole	1492-CJN6-10	20	1492-CJN6-10	20	1492-CJN6-10	20			
Screw Center Jumper — 4-pole	1492-CJN6-4	50	1492-CJN6-4	50	1492-CJN6-4	50			
Screw Center Jumper — 3-pole	1492-CJN6-3	50	1492-CJN6-3	50	1492-CJN6-3	50			
Screw Center Jumper — 2-pole	1492-CJN6-2	50	1492-CJN6-2	50	1492-CJN6-2	50			
Other Accessories:									
Test Plug Socket	1492-TPS23	20	1492-TPS23	20	1492-TPS23	20			
Test Plug	1492-TP23	20	1492-TP23	20	1492-TP23	20			
Neutral Connection Block (4 mm) Blue*	1492-JNC4-B	50	—	—	—	—			
Neutral Bus Bar (1 m)	1492-NBB3-1M	5	—	—	—	—			
Marking Systems:									
Snap-in Marker Cards	1492-M6X5 (200/card)	5	1492-M6X5 (200/card)	5	1492-M6X5 (200/card)	5			

* These terminals mount on the 1492-NBB3-1M Neutral Busbar. They can accept 1492-M6X5 snap-in markers.