

Spring-Clamp Connection Terminal Blocks

Standard Feed-Through Blocks

	1492-L4				1492-L4T				1492-L4Q			
Dimensions are not intended to be used for manufacturing purposes. Note: Height dimension is measured from top of rail to top of terminal block.												
Specifications	<i>Feed-through terminal block</i>				<i>Feed-through terminal block with 3 connection points, 2 on one side</i>				<i>Feed-through terminal block with 2 connection points on each side</i>			
Certifications		CSA	IEC	ATEX		CSA	IEC	ATEX		CSA	IEC	ATEX
Voltage Rating	600V AC/DC		800V AC/DC	550V AC/DC	600V AC/DC		800V AC/DC	550V AC/DC	600V AC/DC		800V AC/DC	550V AC/DC
Maximum Current	33 A	35 A	32 A	28 A	33 A	35 A	32 A	28 A	33 A	35 A	32 A	28 A
Wire Range (Rated Cross Section)	#26...10 AWG		4 mm ²	4 mm ² (20...10 AWG)	#26...10 AWG		4 mm ²	4 mm ² (20...10 AWG)	#26...10 AWG		4 mm ²	4 mm ² (20...10 AWG)
Wire Strip Length	0.47 in. (12 mm)				0.47 in. (12 mm)				0.47 in. (12 mm)			
Density	49 pcs/ft (163 pcs/m)				49 pcs/ft (163 pcs/m)				49 pcs/ft (163 pcs/m)			
Housing Temperature Range	-58...+248 °F (-50...+120 °C)				-58...+248 °F (-50...+120 °C)				-58...+248 °F (-50...+120 °C)			
Short-Circuit Current Rating	See page 12-78											
Terminal Blocks		Cat. No.	Pkg Qty.		Cat. No.	Pkg Qty.		Cat. No.	Pkg Qty.		Cat. No.	Pkg Qty.
Color	Grey	1492-L4	50		1492-L4T	50		1492-L4Q	50		1492-L4Q	50
	Red	1492-L4-RE	50		1492-L4T-RE	50		1492-L4Q-RE	50		1492-L4Q-RE	50
	Blue	1492-L4-B	50		1492-L4T-B	50		1492-L4Q-B	50		1492-L4Q-B	50
	Black	1492-L4-BL	50		1492-L4T-BL	50		1492-L4Q-BL	50		1492-L4Q-BL	50
	Green	1492-L4-G	50		1492-L4T-G	50		1492-L4Q-G	50		1492-L4Q-G	50
	Yellow	1492-L4-Y	50		1492-L4T-Y	50		1492-L4Q-Y	50		1492-L4Q-Y	50
	Orange	1492-L4-OR	50		1492-L4T-OR	50		1492-L4Q-OR	50		1492-L4Q-OR	50
	Brown	1492-L4-BR	50		1492-L4T-BR	50		1492-L4Q-BR	50		1492-L4Q-BR	50
	White	1492-L4-W	50		1492-L4T-W	50		1492-L4Q-W	50		1492-L4Q-W	50
Accessories		Cat. No.	Pkg Qty.		Cat. No.	Pkg Qty.		Cat. No.	Pkg Qty.		Cat. No.	Pkg Qty.
Mounting Rails												
1 m Symmetrical DIN (Steel)		199-DR1	10		199-DR1	10		199-DR1	10		199-DR1	10
1 m Symmetrical DIN (Aluminum)		1492-DR5	10		1492-DR5	10		1492-DR5	10		1492-DR5	10
1 m Hi-Rise Sym. DIN (Aluminum)		1492-DR6	2		1492-DR6	2		1492-DR6	2		1492-DR6	2
1 m Angled Hi-Rise Sym. DIN (Steel)		1492-DR7	2		1492-DR7	2		1492-DR7	2		1492-DR7	2
End Barriers	Grey	1492-EBL4	50		1492-EBL4T	50		1492-EBL4Q	50		1492-EBL4Q	50
	Blue	1492-EBL4-B	50		1492-EBL4T-B	50		1492-EBL4Q-B	50		1492-EBL4Q-B	50
	Yellow	1492-EBL4-Y	50		1492-EBL4T-Y	50		1492-EBL4Q-Y	50		1492-EBL4Q-Y	50
End Anchors and Retainers												
Screwless End Retainer		1492-ERL35	20		1492-ERL35	20		1492-ERL35	20		1492-ERL35	20
DIN Rail — Normal Duty		1492-EAJ35	100		1492-EAJ35	100		1492-EAJ35	100		1492-EAJ35	100
DIN Rail — Heavy Duty		1492-EAHJ35	50		1492-EAHJ35	50		1492-EAHJ35	50		1492-EAHJ35	50
Jumpers:												
Plug-in Center Jumper — 10-Pole		1492-CJK6-10	20		1492-CJK6-10	20		1492-CJK6-10	20		1492-CJK6-10	20
Plug-in Center Jumper — 9-Pole		1492-CJK6-9	20		1492-CJK6-9	20		1492-CJK6-9	20		1492-CJK6-9	20
Plug-in Center Jumper — 8-Pole		1492-CJK6-8	20		1492-CJK6-8	20		1492-CJK6-8	20		1492-CJK6-8	20
Plug-in Center Jumper — 7-Pole		1492-CJK6-7	20		1492-CJK6-7	20		1492-CJK6-7	20		1492-CJK6-7	20
Plug-in Center Jumper — 6-Pole		1492-CJK6-6	20		1492-CJK6-6	20		1492-CJK6-6	20		1492-CJK6-6	20
Plug-in Center Jumper — 5-Pole		1492-CJK6-5	20		1492-CJK6-5	20		1492-CJK6-5	20		1492-CJK6-5	20
Plug-in Center Jumper — 4-Pole		1492-CJK6-4	60		1492-CJK6-4	60		1492-CJK6-4	60		1492-CJK6-4	60
Plug-in Center Jumper — 3-Pole		1492-CJK6-3	60		1492-CJK6-3	60		1492-CJK6-3	60		1492-CJK6-3	60
Plug-in Center Jumper — 2-Pole		1492-CJK6-2	60		1492-CJK6-2	60		1492-CJK6-2	60		1492-CJK6-2	60
Other Accessories												
Reducing Sleeves #26...#24 AWG (0.13...0.2 mm ²) White		1492-PSL4-2	100		1492-PSL4-2	100		1492-PSL4-2	100		1492-PSL4-2	100
Reducing Sleeves #20...#22 AWG (0.25...0.5 mm ²) Grey		1492-PSL4-5	100		1492-PSL4-5	100		1492-PSL4-5	100		1492-PSL4-5	100
Reducing Sleeves #18 AWG (0.75...1.0 mm ²) Dark Grey		1492-PSL4-10	100		1492-PSL4-10	100		1492-PSL4-10	100		1492-PSL4-10	100
Test Plug												
Test Plug (Stackable)		1492-TP23	20		1492-TP23	20		1492-TP23	20		1492-TP23	20
Electrical Warning Plate		1492-TPL6	25		1492-TPL6	25		1492-TPL6	25		1492-TPL6	25
Marking Systems												
Snap-In Marker Cards		1492-EWPL6	20		1492-EWPL6	20		1492-EWPL6	20		1492-EWPL6	20
Snap-In Marker Cards		1492-M6X10 (120/card)	5		1492-M6X10 (120/card)	5		1492-M6X10 (120/card)	5		1492-M6X10 (120/card)	5
Snap-In Marker Cards		1492-M6X5 (200/card)	5		1492-M6X5 (200/card)	5		1492-M6X5 (200/card)	5		1492-M6X5 (200/card)	5
Hinged Marker Cards		1492-MH6X12 (80/card)	5		1492-MH6X12 (80/card)	5		1492-MH6X12 (80/card)	5		1492-MH6X12 (80/card)	5