

Spring-Clamp Connection Terminal Blocks

Specialty Feed-Through Blocks

	1492-LD2C			1492-LD3C				1492-LD4C		
Dimensions are not intended to be used for manufacturing purposes. Note: Height dimension is measured from top of rail to top of terminal block.										
	Two-level feed-through terminal block with commoning bar			Two-level feed-through terminal block with commoning bar				Two-level feed-through terminal block with commoning bar		
Specifications										
Certifications										
Voltage Rating	300V AC/DC 600V AC/DC 500V AC/DC			600V AC/DC 800V AC/DC 550V AC/DC				600V AC/DC 800V AC/DC		
Maximum Current	10 A 17.5 A			20 A 25 A 24 A 22 A				25 A 30 A 32 A		
Wire Range (Rated Cross Section)	#28...16 AWG 1.5 mm ²			#30...12 AWG 2.5 mm ² 0.5...2.5 mm ² (#20...14 AWG)				#26...10 AWG 4 mm ²		
Wire Strip Length	0.39 in. (10 mm)			0.39 in. (10 mm)				0.39 in. (10 mm)		
Density	87 pcs/ft (285 pcs/m)			59 pcs/ft (196 pcs/m)				49 pcs/ft (163 pcs/m)		
Housing Temperature Range	-58...+248 °F (-50...+120 °C)			-58...+248 °F (-50...+120 °C)				-58...+248 °F (-50...+120 °C)		
Terminal Blocks		Cat. No.	Pkg Qty.		Cat. No.	Pkg Qty.		Cat. No.	Pkg Qty.	
Color: Grey		1492-LD2C	50		1492-LD3C	25		1492-LD4C	25	
Accessories		Cat. No.	Pkg Qty.		Cat. No.	Pkg Qty.		Cat. No.	Pkg Qty.	
Mounting Rails:										
1 m Symmetrical DIN (Steel)		199-DR1	10		199-DR1	10		199-DR1	10	
1 m Symmetrical DIN (Aluminum)		1492-DR5	10		1492-DR5	10		1492-DR5	10	
1 m Hi-Rise Sym. DIN (Aluminum)		1492-DR6	2		1492-DR6	2		1492-DR6	2	
1 m Angled Hi-Rise Sym. DIN (Steel)		1492-DR7	2		1492-DR7	2		1492-DR7	2	
End Barriers Grey		1492-EBLD2	50		1492-EBLD3	20		1492-EBLD4	20	
End Anchors and Retainers										
Screwless End Retainer		1492-ERL35	20		1492-ERL35	20		1492-ERL35	20	
DIN Rail — Normal Duty		1492-EAJ35	100		1492-EAJ35	100		1492-EAJ35	100	
DIN Rail — Heavy Duty		1492-EAHJ35	50		1492-EAHJ35	50		1492-EAHJ35	50	
Jumpers:										
Plug-in Center Jumper — 50-Pole		—	—		1492-CJK5-50	10		—	—	
Plug-in Center Jumper — 10-Pole		1492-CJL4-10	20		1492-CJK5-10	20		1492-CJK6-10	20	
Plug-in Center Jumper — 9-Pole		—	—		1492-CJK5-9	20		1492-CJK6-9	20	
Plug-in Center Jumper — 8-Pole		—	—		1492-CJK5-8	20		1492-CJK6-8	20	
Plug-in Center Jumper — 7-Pole		—	—		1492-CJK5-7	20		1492-CJK6-7	20	
Plug-in Center Jumper — 6-Pole		—	—		1492-CJK5-6	20		1492-CJK6-6	20	
Plug-in Center Jumper — 5-Pole		1492-CJL4-5	60		1492-CJK5-5	20		1492-CJK6-5	20	
Plug-in Center Jumper — 4-Pole		1492-CJL4-4	60		1492-CJK5-4	60		1492-CJK6-4	60	
Plug-in Center Jumper — 3-Pole		1492-CJL4-3	60		1492-CJK5-3	60		1492-CJK6-3	60	
Plug-in Center Jumper — 2-Pole		1492-CJL4-2	60		1492-CJK5-2	60		1492-CJK6-2	60	
Other Accessories:										
Reducing Sleeves 28...24 AWG (0.13...0.2 mm ²) White		1492-PSL2-2	100		1492-PSLS2-2	100		—	—	
Reducing Sleeves 22...20 AWG (0.13...0.2 mm ²) Grey		1492-PSL2-5	100		1492-PSLS2-5	100		—	—	
Test Plug		1492-TPL4	25		—	—		1492-TP23	20	
Electrical Warning Plate		1492-EWPL4	20		—	—		1492-EWPL6	20	
Group Marking Carrier		1492-GM35	25		1492-GM35	25		1492-GM35	25	
Marking Systems:										
Snap-In Marker Cards		1492-M3X12 (120/card)*	5		1492-M5X10 (144/card)	5		1492-M6X10 (120/card)	5	
Snap-In Marker Cards		1492-M3X5 (100/card)	5		1492-M5X5 (200/card)	5		1492-M6X5 (200/card)	5	

* May only be mounted in terminal block corner marking positions.