

Spring-Clamp Connection Terminal Blocks

Grounding Blocks, Continued

	1492-LG3				1492-LG3T				1492-LG3Q			
Dimensions are not intended to be used for manufacturing purposes. Note: Height dimension is measured from top of rail to top of terminal block.												
Specifications	<i>Feed-through Ground Block</i>				<i>Feed-through Ground Block with 2 points on one side</i>				<i>Feed-through Ground Block with 2 points on each side</i>			
Certifications												
Voltage Rating	—				—				—			
Maximum Current	Grounding				Grounding				Grounding			
Wire Range (Rated Cross Section)	#30...12 AWG	#26...12 AWG	2.5 mm ²	2.5 mm ² (20...12 AWG)	#30...12 AWG	#26...12 AWG	2.5 mm ²	2.5 mm ² (20...12 AWG)	#30...12 AWG	#26...12 AWG	2.5 mm ²	2.5 mm ² (20...12 AWG)
Wire Strip Length	0.39 in. (10 mm)				0.39 in. (10 mm)				0.39 in. (10 mm)			
Density	59 pcs/ft (196 pcs/m)				59 pcs/ft (196 pcs/m)				59 pcs/ft (196 pcs/m)			
Housing Temperature Range	-58...+248 °F (-50...+120 °C)				-58...+248 °F (-50...+120 °C)				-58...+248 °F (-50...+120 °C)			
Terminal Blocks	Cat. No.		Pkg Qty.		Cat. No.		Pkg Qty.		Cat. No.		Pkg Qty.	
Color: Green/Yellow	1492-LG3		50		1492-LG3T		50		1492-LG3Q		50	
Accessories	Cat. No.		Pkg Qty.		Cat. No.		Pkg Qty.		Cat. No.		Pkg Qty.	
Mounting Rails:												
1 m Symmetrical DIN (Steel)	199-DR1		10		199-DR1		10		199-DR1		10	
1 m Symmetrical DIN (Aluminum)	1492-DR5		10		1492-DR5		10		1492-DR5		10	
1 m Hi-Rise Symmetrical DIN (Aluminum)	1492-DR6		2		1492-DR6		2		1492-DR6		2	
1 m Symmetrical Heavy Duty DIN (Steel)	199-DR9		5		199-DR9		5		199-DR9		5	
End Barrier Yellow	1492-EBL3-Y		50		1492-EBL3T-Y		50		1492-EBL3Q-Y		50	
End Anchors and Retainers:												
Screwless End Retainer	1492-ERL35		20		1492-ERL35		20		1492-ERL35		20	
DIN Rail — Normal Duty	1492-EAJ35		100		1492-EAJ35		100		1492-EAJ35		100	
DIN Rail — Heavy Duty	1492-EAHJ35		50		1492-EAHJ35		50		1492-EAHJ35		50	
Other Accessories:												
Reducing Sleeves 30...24 AWG (0.13...0.2 mm ²) White	1492-PSL3-2		100		1492-PSL3-2		100		1492-PSL3-2		100	
Reducing Sleeves 22...20 AWG (0.25...0.5 mm ²) Grey	1492-PSL3-5		100		1492-PSL3-5		100		1492-PSL3-5		100	
Reducing Sleeves 18 AWG (0.75...1.0 mm ²) Dark Grey	1492-PSL3-10		100		1492-PSL3-10		100		1492-PSL3-10		100	
Test Plug	1492-TP23		20		1492-TP23		20		1492-TP23		20	
Test Plug (Stackable)	1492-TPL5		25		1492-TPL5		25		1492-TPL5		25	
Group Marking Carrier	1492-GM35		25		1492-GM35		25		1492-GM35		25	
Marking Systems:												
Snap-In Marker Cards	1492-M5X10 (144/card)		5		1492-M5X10 (144/card)		5		1492-M5X10 (144/card)		5	
Snap-In Marker Cards	1492-M5X5 (200/card)		5		1492-M5X5 (200/card)		5		1492-M5X5 (200/card)		5	
Hinged Marker Cards	1492-MH5X10 (96/card)		5		1492-MH5X10 (96/card)		5		1492-MH5X10 (96/card)		5	
Hinged Marker Cards	1492-MH5X15 (96/card)		5		1492-MH5X15 (96/card)		5		1492-MH5X15 (96/card)		5	