

Screw Connection Terminal Blocks

Space-Saver Grounding Blocks

	1492-WG4				1492-WG6				1492-WG10S		
Dimensions are not intended to be used for manufacturing purposes. Note: Height dimension is measured from top of rail to top of terminal block.											
	Single-circuit grounding terminal block.				Single-circuit grounding terminal block.				Single-circuit grounding terminal block.		
Specifications											
Certifications		IEC	CSA	ATEX		IEC	CSA	ATEX		CSA	IEC
Voltage Rating	—	—	—	—	—	—	—	—	—	—	—
Maximum Current	Grounding				Grounding				Grounding		
Wire Range (Rated Cross Section)	#22... 12 AWG	4 mm ²	#22... 12 AWG	4 mm ²	#22... 10 AWG	6 mm ²	#22... 10 AWG	6 mm ²	#22... 8 AWG	#22... 8 AWG	10 mm ²
Wire Strip Length	0.43 in. (11 mm)				0.47 in. (12 mm)				0.43 in (11 mm)		
Recommended Tightening Torque	5.6...6.8 lb•in. (0.7 N•m)				5.6...6.8 lb•in. (0.7 N•m)				7.1 lb•in (0.8 N•m)		
Density	50 pcs/ft (166 pcs/m)				43 pcs/ft (142 pcs/m)				38 pcs/ft (125 pcs/m)		
Housing Temperature Range	-40...+195 °F (-40...+90 °C)				-40...+195 °F (-40...+90 °C)				-40...+195 °F (-40...+90 °C)		
Terminal Blocks		Cat. No.		Pkg Qty.		Cat. No.		Pkg Qty.		Cat. No.	Pkg Qty.
Color: Green/Yellow		1492-WG4		50		1492-WG6		50		1492-WG10S	—
Accessories		Cat. No.		Pkg Qty.		Cat. No.		Pkg Qty.		Cat. No.	Pkg Qty.
Mounting Rails:											
1 m Symmetrical DIN (Steel)		199-DR1		10		199-DR1		10		199-DR1	10
1 m Symmetrical DIN (Aluminum)		1492-DR5		10		1492-DR5		10		1492-DR5	10
1 m Hi-Rise Sym. DIN (Aluminum)		1492-DR6		2		1492-DR6		2		1492-DR6	2
1 m Angled Hi-Rise Sym. DIN (Steel)		1492-DR7		2		1492-DR7		2		1492-DR7	2
End Barrier		1492-EB3-Y		50		1492-EB10-Y		50		1492-EB10-Y	50
End Anchors:											
DIN Rail — Normal Duty		1492-EAJ35		100		1492-EAJ35		100		1492-EAJ35	100
DIN Rail — Heavy Duty		1492-EAHJ35		50		1492-EAHJ35		50		1492-EAHJ35	50
Other Accessories:											
Group Marking Carrier		1492-GM35		25		1492-GM35		25		1492-GM35	25
Marking Systems:											
Snap-in Marker Card		1492-MS6X12 (80/card)		5		1492-MS6X12 (80/card)		5		1492-MS6X12 (80/card)	5