

IEC Terminal Block Accessories

Specifications

In general, accessories for terminal blocks are not eligible for recognition by UL, CSA, or other third party approval agencies. The suitability of the installation must be judged in the end use application due to the wide variety of possible uses. However, accessories are designed to meet, and are tested to, the terminal block assembly requirements such as electrical spacings, etc.

Maximum number of multiple wire connections for copper conductors of the same cross-section and type for Allen-Bradley IEC Terminal Blocks.

Cat. Nos. 1492-J and L products are all recommended for one conductor per terminal. Wire range is defined in the cat. page for each of the products.

Cat. No.	Wire Size [AWG]																		
	#30	#28	#26	#24	#22	#20	#18	#16	#14	#12	#10	#8	#6	#4	#2	#1	1/0	2/0	3/0
	Number of the Same Size Wires Per Terminal																		
1492-H4	—	—	—	—	4	4	3	2	2	1	—	—	—	—	—	—	—	—	—
1492-H5	—	—	—	—	4	4	3	2	2	1	—	—	—	—	—	—	—	—	—
1492-H6	—	—	—	—	4	4	3	2	2	1	—	—	—	—	—	—	—	—	—
1492-H7	—	—	—	—	4	4	3	2	2	1	—	—	—	—	—	—	—	—	—
1492-J2Q	—	—	4	4	4	3	1	1	1	—	—	—	—	—	—	—	—	—	—
1492-J3	4	4	4	4	4	4	3	3	2	1	—	—	—	—	—	—	—	—	—
1492-J3F	4	4	4	4	4	4	3	3	2	1	—	—	—	—	—	—	—	—	—
1492-J3TW (Single Side)	4	4	4	4	4	4	3	3	2	1	—	—	—	—	—	—	—	—	—
1492-J3TW (Twin Side)	—	—	4	4	4	3	1	1	1	—	—	—	—	—	—	—	—	—	—
1492-J4	—	—	—	—	4	4 (29 A)	3	3	2	1	1	—	—	—	—	—	—	—	—
1492-J4M	—	—	—	—	4	4 (29 A)	3	3	2	1	1	—	—	—	—	—	—	—	—
1492-J6	—	—	—	—	4	4 (30 A)	3	3	3	2	1	1	—	—	—	—	—	—	—
1492-J10	—	—	—	—	4	4	4	4 (46 A)	3 (50 A)	2 (50 A)	1	1	1	—	—	—	—	—	—
1492-J16	—	—	—	—	—	—	—	4 (67 A)	4 (62 A)	3 (71 A)	2 (67 A)	1	1	1	—	—	—	—	—
1492-J35	—	—	—	—	—	—	—	—	3	3	3 (90 A)	2	2 (114 A)	1	1	1	1	—	—
1492-J50	—	—	—	—	—	—	—	—	—	—	—	2	2	1	1	1	1	—	—
1492-J70*	—	—	—	—	—	—	—	—	5	5	5	2	2	2	1	1	1	1	—
1492-JC3	—	—	4	4	4	3	1	1	1	—	—	—	—	—	—	—	—	—	—
1492-JD3...	4	4	4	4	4	4	3	2	2	1	—	—	—	—	—	—	—	—	—
1492-JD3F	4	4	4	4	4	4	3	2	2	1	—	—	—	—	—	—	—	—	—
1492-JD3P	—	—	—	—	4	4	3	2	1	1	—	—	—	—	—	—	—	—	—
1492-JDC3	4	4	4	4	4	4	3	2	2	1	—	—	—	—	—	—	—	—	—
1492-JDG3	4	4	4	4	4	4	3	2	2	1	—	—	—	—	—	—	—	—	—
1492-JDG3P	—	—	—	—	4	4	3	2	1	1	—	—	—	—	—	—	—	—	—
1492-JG2Q	—	—	4	4	4	3	1	1	1	—	—	—	—	—	—	—	—	—	—
1492-JG3	4	4	4	4	4	4	3	3	2	1	—	—	—	—	—	—	—	—	—