

	1492-WMG3	1492-WMG4		
<p>Dimensions are not intended to be used for manufacturing purposes.</p> <p>Note: Height dimension is measured from top of rail to top of terminal block.</p>				
Specifications	Single-circuit mini grounding terminal block.	Single-circuit mini grounding terminal block.		
Certifications	IEC	UL, IEC		
Maximum Current	Grounding	Grounding		
Wire Range (Rated Cross Section)	#14 AWG (2.5 mm ²)	#22...12 AWG 0.5...4.0 mm ²		
Wire Strip Length	0.31 in. (8 mm)	0.39 in. (10 mm)		
Recommended Tightening Torque	6.2 lb•in. (0.7 N•m)	5.3 lb•in. (0.6 N•m)		
Density	50 pcs/ft (166 pcs/m)	50 pcs/ft (166 pcs/m)		
Housing Temperature Range	—	-40...+195 °F (-40...+90 °C)		
Terminal Blocks	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.
Color: Metallic	1492-WMG3	50	—	—
Green/Yellow	—	—	1492-WMG4	10
Accessories	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.
Mounting Rails: 1 m Sym. Mini DIN (Steel)	1492-DR3	5	1492-DR3	5
End Anchors and Retainers: Mini Screwless End Retainer	—	—	1492-ERL15	20
Mini DIN Anchor — Normal Duty	—	—	1492-EAJ15	50
Other Accessories: Partition Plate	1492-PPM3	50	1492-PPM3	50
Marking Systems: Snap-in Marker Card	—	—	1492-MS6X9 (80/card)	5
Individual Marker Tab (single character)*	—	—	1492-MP(10/stick)	10

* Cat. no. is incomplete. See page 12-82.