



Screw Connection Terminal Blocks

Sensor Blocks

1492-WTF3...

1492-WTS3...

Dimensions are not intended to be used for manufacturing purposes.
Note: Height dimension is measured from top of rail to top of terminal block.



Specifications	Three-circuit terminal block.			Three-level sensor block.		
Certifications		CSA	IEC		CSA	IEC
Voltage Rating	300V AC/DC		250V AC/DC	300V AC/DC		250V AC/DC
Maximum Current	10 A		24 A	10 A		24 A
Wire Range (Rated Cross Section)	#26...14 AWG		0.5... 2.5 mm ²	#26...14 AWG		0.5... 2.5 mm ²
Recommended Tightening Torque	4.2...4.6 lb•in. (0.5 N•m)			4.2...4.6 lb•in. (0.5 N•m)		
Density	60 pcs/ft (197 pcs/m)			60 pcs/ft (197 pcs/m)		
Housing Temperature Range	-40...+195 °F (-40...+90 °C)			-40...+195 °F (-40...+90 °C)		
Indicator Type WTF3/WTS3	No Indicator			No Indicator		
WTF3LP/WTS3LP	Red LED for PNP devices (10...50V)			Red LED for PNP devices (10...50V)		
WTF3LN/WTS3LN	Red LED for NPN devices (10...50V)			Red LED for NPN devices (10...50V)		
Leakage Current WTF3/WTS3	—			—		
WTF3LP/WTS3LP	2.69 mA @ 50V			2.69 mA @ 50V		
WTF3LN/WTS3LN	2.69 mA @ 50V			2.69 mA @ 50V		
Wire Strip Length	0.31 in. (8 mm)			0.31 in. (8 mm)		
Short-Circuit Current Rating	See page 12-43					

Terminal Blocks		Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.
Color:	Grey	1492-WTF3	50	1492-WTS3	50
	Blue	—	—	1492-WTS3-B	50
	Grey for PNP devices	1492-WTF3LP	50	1492-WTS3LP	50
	Grey for NPN devices	1492-WTF3LN	50	1492-WTS3LN	50
Accessories		Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.
Mounting Rails:					
1 m Symmetrical DIN (Steel)		199-DR1	10	199-DR1	10
1 m Symmetrical DIN (Aluminum)		1492-DR5	10	1492-DR5	10
1 m Hi-Rise Sym. DIN (Aluminum)		1492-DR6	2	1492-DR6	2
1 m Angled Hi-Rise Sym. DIN (Steel)		1492-DR7	2	1492-DR7	2
End Barrier		1492-EBTF3	50	1492-EBTS3	50
End Anchors and Retainers:					
Screwless End Retainer		1492-ERL35	20	1492-ERL35	20
DIN Rail — Normal Duty		1492-EAJ35	100	1492-EAJ35	100
DIN Rail — Heavy Duty		1492-EAHJ35	50	1492-EAHJ35	50
Jumpers:					
Center Jumper — 50-pole		1492-CJT5-50	5	1492-CJT5-50	5
Center Jumper — 10-pole		1492-CJT5-10	10	1492-CJT5-10	10
Center Jumper — 3-pole		1492-CJT5-3	10	1492-CJT5-3	10
Center Jumper — 2-pole		1492-CJT5-2	10	1492-CJT5-2	10
Center Jumper Link		1492-CJL5	10	1492-CJL5	10
Center Jumper Cover — Red		1492-CJCR5	10	1492-CJCR5	10
Center Jumper Cover — Blue		1492-CJCB5	10	1492-CJCB5	10
Side — 20-pole Insulated Red		1492-SJT5-20-R	10	1492-SJT5-20-R	10
Side — 20-pole Insulated Blue		1492-SJT5-20-B	10	1492-SJT5-20-B	10
Other Accessories:					
Partition Plate		1492-PPTS3	50	1492-PPTS3	50
Test Plug Adapter		1492-TA285	10	1492-TA285	10
Electrical Warning Plate	4-Pole	1492-EWP5-4	10	1492-EWP5-4	10
	1-Pole	1492-EWP5	10	1492-EWP5	10
Group Marking Carrier		1492-GM35	25	1492-GM35	25
Marking Systems:					
Snap-in Marker Card		1492-MS5X9 (80/card)	5	1492-MS5X9 (80/card)	5