

Safety Disconnect Switches — Hazardous Locations

Product Overview/Product Selection

1



Bulletin 1494G Safety Switch — Hazardous Locations

- 100 A switch rating for use in 30, 60, and 100 A applications
- Type 3R, 7 & 9 bolted enclosure with breather and drain
- For use in Class I, Div. 1 & 2, Groups C & D hazardous gas or vapor locations
- Non-fusible version only
- Viewing window provided as standard to readily see the blades of the disconnect switch
- Auxiliary contact provided as standard
- Lockable handle
- Provisions for a mechanical key interlock switch (trapped key, kirk key, etc.)
- Hinged cover for easy access

Table of Contents

Product Selection this page
 Approximate Dimensions this page

Standards Compliance

UL 1203
 CSA C22.2, No. 25 and 30

Certifications

cULus Listed (File No. E239523, Guide No. WPRP)

Product Selection

Size [A]	Horsepower					Type 3R, 7 & 9 Bolted Enclosure Class I, Div. 1 & 2, Groups C & D Class II, Groups E, F, G
	480V AC		600V AC		250V AC	
	Std.	Max.	Std.	Max.		Cat. No.
30	5	15	7.5	20	5	1494G-DH3N-203W
60	15	30	15	50	10	
100	20	60	30	75	20	

Approximate Dimensions

Approximate dimensions are shown in inches (millimeters). Dimensions are not intended to be used for manufacturing purposes.

