



PRIMARY SIDE




10-32 PHIL-SLOT-5/16" HEX WITH SEMS WASHER


LABEL 40022-417




PRIMARY IDENTIFICATION LABEL



SECONDARY IDENTIFICATION LABEL



IND. BOX LABEL



BULLETIN 1497B

CONTROL TRANSFORMER



Listed 702X

1K0VA


PRIMARY: 240x480

SECONDARY: 120x240

FREQUENCY: 50Hz / 60Hz

MADE IN USA

CAT. **1497B-A11-M14-0-N** SER. **A**




10662074621900
4911

Transformer Specifications

PRIMARY VOLTAGE(S)	240x480
SECONDARY VOLTAGE(S)	120x240
RATED V.A.	1000
RATED FREQUENCY	50/60
INSULATION CLASS	130
AGENCY APPROVALS	UL, CUL
ESTIMATED WEIGHT	38.2 LBS

PRIMARY SIDE N/A • SECONDARY SIDE • N/A



N/A • N/A


CONNECTION DIAGRAM

NOTE:

1. ALL MEASUREMENTS IN INCHES (MM)
2. TORQUE ALL LEAD TO TERMINAL CONNECTIONS AT 30 IN.LBS.

SECONDARY SIDE

PRIMARY SIDE



MAIN PRODUCT IDENTIFICATION LABEL



INDUSTRIAL CONTROL TRANSFORMER

CAT. **1497B-A11-M14-0-N** SER. **A** K.V.A. **1.0**

PRIMARY **240X480** TEMP.CL.°C **130°**

SECONDARY **120X240** FREQUENCY **50/60Hz**

MADE IN USA 49111

Listed 702X

LABEL 40022-417

USE MIN 105°C INSULATED WIRE
(1) OR (2) No. 18-12 AWG STR. Cu WIRE ONLY
TORQUE TERMINALS TO 30 LB-IN

PACKAGED ACCESSORIES

1	2 PAIR OF JUMPERS
-	-
-	-

DATE	10/1/09	DRAWN	J.G.V.	CHECKED		APPROVED	
RELEASE DATE		CUSTOMER PART NO.	ROCKWELL #1497B-A11-M14-0-N				
DATE	12/5/11	BY	PJA	REVISIONS		SIZE	C
DATE	10/1/09	BY	J.V.	REVISIONS	B	SCALE	NONE

REMOVE TEST SPECS. (NOW ON COIL DWG)	PJA	12/5/11
B REDRAWN	AN003984	J.V. 10/1/09
ECL	REVISIONS	BY DATE