

**AB** BULLETIN **1497A**  
 Rockwell Automation, 1201  
 S 2nd St, Milwaukee, WI  
 53204, USA

**150 VA PRIMARY:**  
 220X440  
 230X460  
 240X480

**SECONDARY:**  
 110  
 115  
 120

**FREQUENCY:**  
 50Hz / 60Hz

**CONTROL TRANSFORMER**


**UL** Listed 702X **US**

**PRODUCT OF USA**

CAT. **1497A-A4-M6-3-N** SER. **A**

10662074694003

Transformer Specifications	
PRIMARY VOLTAGE(S)	230x460 (TRIPLE RATED)
SECONDARY VOLTAGE(S)	115
RATED V.A.	150
RATED FREQUENCY	50/60
INSULATION CLASS	130
AGENCY APPROVALS	UL, CUL
ESTIMATED WEIGHT	5.3 LBS





SEC.FUSECLIPS INTERNALLY JUMPERED  
 CONNECTION DIAGRAM

**NOTES:**

1. ALL MEASUREMENTS IN INCHES (MM)
2. TERMINAL SCREWS ARE COMBO #8-32 PHIL-SLOT-1/4" HEX WITH SEMS WASHER.
3. 2 POLE, CLASS "CC" PRIMARY FUSE BLOCK, ACCOMMODATES TWO 13/32" X 1-1/2" CLASS "CC" FUSES.
4. SECONDARY FUSE CLIP ACCOMMODATES ONE 13/32" X 1-1/2" MIDGET FUSE.

**H1F H4F**



**INDUSTRIAL CONTROL TRANSFORMER**

CAT. **1497A-A4-M6-3-N** SER. **A** K.V.A. **0.150**

PRIMARY **220 x 440 , 230 x 460 , 240 x 480** TEMP.CL. °C **130°**



SECONDARY **110 , 115 , 120** FREQUENCY **50/60Hz**

**Allen-Bradley** **UL** Listed 702X **Product of USA** 45195

PACKAGED ACCESSORIES			
1	PAIR OF JUMPERS		
-	-		

MICRON INDUSTRIES CORPORATION  
 1211 W 22nd STREET, SUITE 200, BAK BRIDGE, ILL  
 Tel: (800)664-4660, (630)516-1222 Fax: (630)516-1820  
 www.MicronPower.com

DATE	11/13/19	DRAWN	JAV	CHECKED		APPROVED	
RELEASE DATE		CUSTOMER PART NO.	ROCKWELL #1497A-A4-M6-3-N				
QTY. P/N	B150BTZ13RBF A3-1						
SIZE	C	SCALE	NONE				
B150BTZ13RBF							



USE MIN 105°C INSULATED WIRE  
 (1) OR (2) No. 18-12 AWG STR. Cu WIRE ONLY  
 (1) No. 16/18 AWG STR. Cu WIRE ONLY  
 TORQUE TERMINALS TO 16 LB-IN

B	CONV. FROM BASE MODEL	AN006685	DB	6/24/21
A	I3 CONSTR/BASE	AN006460	JW	11/13/19
ECL	REVISIONS		BY	DATE