




AB BULLETIN **1497A**

Rockwell Automation, 1201
S 2nd St, Milwaukee, WI
53204, USA

300 VA
PRIMARY:
230X460

SECONDARY:
115

CONTROL
TRANSFORMER

FREQUENCY:
50Hz / 60Hz


PRODUCT OF USA

CAT. **1497A-A7-M6-3-N** SER. **A**

10662074694034



UL US Listed 702X

Transformer Specifications	
PRIMARY VOLTAGE(S)	230x460 (TRIPLE RATED)
SECONDARY VOLTAGE(S)	115
RATED V.A.	300
RATED FREQUENCY	50/60
INSULATION CLASS	130
AGENCY APPROVALS	UL, CUL
ESTIMATED WEIGHT	11.0 LBS



NOTES:



1. ALL MEASUREMENTS IN INCHES (MM)
2. TERMINAL SCREWS ARE COMBO #8-32 PHIL-SLOT-1/4" HEX WITH SEMS WASHER.
3. 2 POLE, CLASS "CC" PRIMARY FUSE BLOCK, ACCOMMODATES TWO 13/32" X 1-1/2" CLASS "CC" FUSES.
4. SECONDARY FUSE CLIP ACCOMMODATES ONE 13/32" X 1-1/2" MIDGET FUSE.



INDUSTRIAL CONTROL TRANSFORMER			
CAT.	SER.	K.V.A.	
1497A-A7-M6-3-N	A	0.300	
PRIMARY		TEMP.CL.°C	
220 x 440, 230 x 460, 240 x 480		130°	
SECONDARY		FREQUENCY	
110, 115, 120		50/60Hz	

Allen-Bradley UL US Listed 702X Product of USA

USE MIN 105°C INSULATED WIRE
(1) OR (2) No. 18-12 AWG STR. Cu WIRE ONLY
(1) No. 16/18 AWG STR. Cu WIRE ONLY
TORQUE TERMINALS TO 16 LB-IN



REV.	DESCRIPTION	DATE	BY
B	CONV. FROM BASE MODEL	6/23/21	DB
A	13 CONSTR/BASE	11/14/19	JW
ECL	REVISIONS		

PACKAGED ACCESSORIES			
1	1 PAIR OF JUMPERS		
-	-		

MICRON INDUSTRIES CORPORATION
1201 S 2nd St, Milwaukee, WI 53204
Tel: (414) 444-1400 Fax: (414) 444-1401
www.micronpower.com

DATE: 11/14/19 DRAWN: JAW CHECKED: APPROVED: [Signature]

QTY. P/N: B300BTZ13RBF A3-1

SIZE: C SCALE: NONE