



# DRAWING FOR 10.50" X 27.50" NEMA TYPE 12/3R/4 PAINTED ENCLOSURE



BOTTOM VIEW

THIS DWG APPLIES TO:

- BUL. 502-502L - NEMA SIZE 0-1-2
- BUL. 503-503L - NEMA SIZE 0-1-2
- BUL. 506X - NEMA SIZE 0-1-2  
100A 250V MAX.  
60A-600V MAX.  
130 VA CONTROL TRANSFORMER MAX.
- BUL. 507X - NEMA SIZE 0-1-2  
130 VA CONTROL TRANSFORMER MAX.
- BUL. 512 - NEMA SIZE 0-1-2  
100A-250V MAX.  
60A-600V MAX.
- BUL. 513 - NEMA SIZE 0-1-2

NOTES:

1. ALL DIM'S. SHOWN IN PARENTHESES ARE IN MILLIMETERS.
2. ALL DIM'S. ARE APPROXIMATE AND NOT INTENDED FOR MANUFACTURING PURPOSES