

LEVEL	I/O CAT. NO.	MODULE LABEL																															
UPPER	1746-IB32, 1769-IQ32T SINK	COM 3	COM 3	IN 16	IN 17	IN 18	IN 19	IN 20	IN 21	IN 22	IN 23	IN 24	IN 25	IN 26	IN 27	IN 28	IN 29	IN 30	IN 31	COM 4	COM 4												
LOWER		COM 1	COM 1	IN 0	IN 1	IN 2	IN 3	IN 4	IN 5	IN 6	IN 7	IN 8	IN 9	IN 10	IN 11	IN 12	IN 13	IN 14	IN 15	COM 2	COM 2												
UPPER		COM 3	COM 3	IN 00	IN 01	IN 02	IN 03	IN 04	IN 05	IN 06	IN 07	IN 10	IN 11	IN 12	IN 13	IN 14	IN 15	IN 16	IN 17	COM 4	COM 4												
LOWER		COM 1	COM 1	IN 00	IN 01	IN 02	IN 03	IN 04	IN 05	IN 06	IN 07	IN 10	IN 11	IN 12	IN 13	IN 14	IN 15	IN 16	IN 17	COM 2	COM 2												
UPPER	1746-IV32, 1769-IQ32T SOURCE	+V 3	+V 3	IN 16	IN 17	IN 18	IN 19	IN 20	IN 21	IN 22	IN 23	IN 24	IN 25	IN 26	IN 27	IN 28	IN 29	IN 30	IN 31	COM 4	COM 4												
LOWER		+V 1	+V 1	IN 0	IN 1	IN 2	IN 3	IN 4	IN 5	IN 6	IN 7	IN 8	IN 9	IN 10	IN 11	IN 12	IN 13	IN 14	IN 15	COM 2	COM 2												
UPPER		+V 3	+V 3	IN 00	IN 01	IN 02	IN 03	IN 04	IN 05	IN 06	IN 07	IN 10	IN 11	IN 12	IN 13	IN 14	IN 15	IN 16	IN 17	COM 4	COM 4												
LOWER		+V 1	+V 1	IN 00	IN 01	IN 02	IN 03	IN 04	IN 05	IN 06	IN 07	IN 10	IN 11	IN 12	IN 13	IN 14	IN 15	IN 16	IN 17	COM 2	COM 2												
UPPER	1769-OB32, 1746-OB32, OV32, OB32E	+V 2	+V 2	OUT 16	OUT 17	OUT 18	OUT 19	OUT 20	OUT 21	OUT 22	OUT 23	OUT 24	OUT 25	OUT 26	OUT 27	OUT 28	OUT 29	OUT 30	OUT 31	COM 2	COM 2												
LOWER		+V 1	+V 1	OUT 0	OUT 1	OUT 2	OUT 3	OUT 4	OUT 5	OUT 6	OUT 7	OUT 8	OUT 9	OUT 10	OUT 11	OUT 12	OUT 13	OUT 14	OUT 15	COM 1	COM 1												
UPPER	1769-OB32P	+V 2	+V 2	OUT 00	OUT 01	OUT 02	OUT 03	OUT 04	OUT 05	OUT 06	OUT 07	OUT 10	OUT 11	OUT 12	OUT 13	OUT 14	OUT 15	OUT 16	OUT 17	COM 2	COM 2												
LOWER		+V 1	+V 1	OUT 00	OUT 01	OUT 02	OUT 03	OUT 04	OUT 05	OUT 06	OUT 07	OUT 10	OUT 11	OUT 12	OUT 13	OUT 14	OUT 15	OUT 16	OUT 17	COM 1	COM 1												
UPPER	1756-IA16I, IB16I, IH16I	IN 0	IN 1	IN 2	IN 3	IN 4	IN 5	IN 6	IN 7	IN 8	IN 9	IN 10	IN 11	IN 12	IN 13	IN 14	IN 15	IN 16	IN 17	COM 2	COM 2												
LOWER		COM 0	COM 0	COM 2	COM 3	COM 4	COM 5	COM 6	COM 7	COM 8	COM 9	COM 10	COM 11	COM 12	COM 13	COM 14	COM 15	COM 16	COM 17	COM 1	COM 1												
UPPER	1756-IB16D TC-IDX16I	IN 0	IN 1	IN 2	IN 3	IN 4	IN 5	IN 6	IN 7	IN 8	IN 9	IN 10	IN 11	IN 12	IN 13	IN 14	IN 15	IN 16	IN 17	COM 2	COM 2												
LOWER		COM 0	COM 0	COM 0	COM 0	COM 1	COM 1	COM 1	COM 2	COM 2	COM 2	COM 3	COM 3	COM 3	COM 3	COM 3	COM 3	COM 3	COM 3	COM 3	COM 3												
UPPER	1756-IA32,IB32, TC-IDD32I	COM 1	COM 1	IN 16	IN 17	IN 18	IN 19	IN 20	IN 21	IN 22	IN 23	IN 24	IN 25	IN 26	IN 27	IN 28	IN 29	IN 30	IN 31	COM 1	COM 1												
LOWER		COM 0	COM 0	IN 0	IN 1	IN 2	IN 3	IN 4	IN 5	IN 6	IN 7	IN 8	IN 9	IN 10	IN 11	IN 12	IN 13	IN 14	IN 15	COM 0	COM 0												
UPPER	1756-IV32	+V 1	+V 1	IN 16	IN 17	IN 18	IN 19	IN 20	IN 21	IN 22	IN 23	IN 24	IN 25	IN 26	IN 27	IN 28	IN 29	IN 30	IN 31	+V 1	+V 1												
LOWER		+V 0	+V 0	IN 0	IN 1	IN 2	IN 3	IN 4	IN 5	IN 6	IN 7	IN 8	IN 9	IN 10	IN 11	IN 12	IN 13	IN 14	IN 15	COM 0	COM 0												
UPPER	1756-OA16I,OB16I, OB16I,OB16IS, TC-ODK16I,ORC16I, ODJ16I	OUT 0	OUT 1	OUT 2	OUT 3	OUT 4	OUT 5	OUT 6	OUT 7	OUT 8	OUT 9	OUT 10	OUT 11	OUT 12	OUT 13	OUT 14	OUT 15	OUT 16	OUT 17	COM 1	COM 1												
LOWER		+V 0	+V 1	+V 2	+V 3	+V 4	+V 5	+V 6	+V 7	+V 8	+V 9	+V 10	+V 11	+V 12	+V 13	+V 14	+V 15	+V 16	+V 17	COM 1	COM 1												
UPPER	1756-OB8EI,OH8I, TC-ODF08I	OUT 0	OUT 0	OUT 1	OUT 1	OUT 2	OUT 2	OUT 3	OUT 3	OUT 4	OUT 4	OUT 5	OUT 5	OUT 6	OUT 6	OUT 7	OUT 7	OUT 8	OUT 8	COM 1	COM 1												
LOWER		+V 0	COM 0	+V 1	COM 1	+V 2	COM 2	+V 3	COM 3	+V 4	COM 4	+V 5	COM 5	+V 6	COM 6	+V 7	COM 7	+V 8	COM 8	COM 1	COM 1												
UPPER	1756-OB16D, TC-ODX16I	OUT 0	OUT 0	OUT 1	OUT 2	OUT 3	OUT 4	OUT 5	OUT 6	OUT 7	OUT 8	OUT 9	OUT 10	OUT 11	OUT 12	OUT 13	OUT 14	OUT 15	OUT 16	COM 1	COM 1												
LOWER		+V 0	+V 0	+V 0	+V 0	+V 0	+V 0	+V 0	COM 0	+V 1	+V 1	+V 1	+V 1	+V 1	+V 1	+V 1	+V 1	+V 1	+V 1	COM 1	COM 1												
UPPER	1756-OB32,OV32E, TC-ODD32I	+V 1	+V 1	OUT 16	OUT 17	OUT 18	OUT 19	OUT 20	OUT 21	OUT 22	OUT 23	OUT 24	OUT 25	OUT 26	OUT 27	OUT 28	OUT 29	OUT 30	OUT 31	COM 1	COM 1												
LOWER		+V 0	+V 0	OUT 0	OUT 1	OUT 2	OUT 3	OUT 4	OUT 5	OUT 6	OUT 7	OUT 8	OUT 9	OUT 10	OUT 11	OUT 12	OUT 13	OUT 14	OUT 15	COM 0	COM 0												
UPPER	1756-OX8I, TC-ORC08I	OUT 0	OUT 0	OUT 1	OUT 1	OUT 2	OUT 2	OUT 3	OUT 3	OUT 4	OUT 4	OUT 5	OUT 5	OUT 6	OUT 6	OUT 7	OUT 7	OUT 8	OUT 8	COM 1	COM 1												
LOWER		+V 0	+V 0	+V 1	+V 1	+V 2	+V 2	+V 3	+V 3	+V 4	+V 4	+V 5	+V 5	+V 6	+V 6	+V 7	+V 7	+V 8	+V 8	COM 1	COM 1												
UPPER	1762-L40AWA(IN), L40BWA(IN), L40BWB(IN) SINK	COM 0	COM 1	IN 16	IN 17	IN 18	IN 19	IN 20	IN 21	IN 22	IN 23	IN 24	IN 25	IN 26	IN 27	IN 28	IN 29	IN 30	IN 31	COM 2	COM 2												
LOWER		COM 0	COM 1	IN 0	IN 1	IN 2	IN 3	IN 4	IN 5	IN 6	IN 7	IN 8	IN 9	IN 10	IN 11	IN 12	IN 13	IN 14	IN 15	COM 2	COM 2												