

LEVEL	I/O CAT. NO.	MODULE LABEL							
UPPER	1746-NI4	2+	2-	C	SH	3+	3-	C	SH
LOWER		0+	0-	C	SH	1+	1-	C	SH
UPPER	1746-NIO4I, -NIO4V, -FIO4I, -FIO4V		O/O	C	SH		O/I	C	SH
LOWER		0+	0-	C	SH	1+	1-	C	SH
UPPER	1746-NO4I, -NO4V	2	C	+V	SH	3	C	-V	SH
LOWER		0	C	+V	SH	1	C	-V	SH
UPPER		2	C		SH	3	C		SH
LOWER		0	C		SH	1	C		SH
UPPER	1756-OF4 TC-OAV041	2	RTN		SH	1	RTN		SH
LOWER		0	RTN		SH	1	RTN		SH
UPPER	1769-IF4 DIFF. VOLTAGE DIFF. CURRENT	2+	2-		SH	3+	3-		SH
LOWER		0+	0-		SH	1+	1-		SH
UPPER	1769-IF4 SNG. END. VLTG. SNG. END. CUR.	2+			SH	3+	COM		SH
LOWER		0+			SH	1+			SH
LOWER	1769-OF2 SNG. END. VLTG. SNG. END. CUR.	0+	COM		SH	1+	COM		SH
UPPER	1771-OFE	3+	3-		SH	4+	4-		SH
LOWER		1+	1-		SH	2+	2-		SH
	NUMERIC	1	2	3	4	5	6	7	8
		9	10	11	12	13	14	15	16
		1	3	5	7	9	11	13	15
		2	4	6	8	10	12	14	16

CUT AT 40mm