

LEVEL	IO CAT. NO.	MODULE LABEL															
UPPER	1769-IA16	COM	IN	IN	IN	IN	IN	IN	IN	IN	IN	IN	IN	IN	IN	COM	
		COM	0	1	2	3	4	5	6	7	8	9	10	11	12	13	
LOWER																	
UPPER	1769-IO16, IO16F SINK	COM	IN	IN	IN	IN	IN	IN	IN	IN	IN	IN	IN	IN	IN	COM	
		COM	1	0	1	2	3	4	5	6	7	8	9	10	11	12	
LOWER																	
UPPER	1769-IO16, IO16F SOURCE	+V	IN	IN	IN	IN	IN	IN	IN	IN	IN	IN	IN	IN	IN	IN	
		+V	1	0	1	2	3	4	5	6	7	8	9	10	11	12	
LOWER																	
UPPER	1769-OA8, OW8	+V	OUT	OUT	OUT	OUT	OUT	OUT	OUT	OUT	OUT	OUT	OUT	OUT	OUT	OUT	
		+V	1	0	1	2	3	4	5	6	7	8	9	10	11	12	
LOWER																	
UPPER	1769-OA16, OW16	+V	OUT	OUT	OUT	OUT	OUT	OUT	OUT	OUT	OUT	OUT	OUT	OUT	OUT	OUT	
		+V	1	0	1	2	3	4	5	6	7	8	9	10	11	12	
LOWER																	
UPPER	POWERFLEX 700H 20C-DA1-A	+V	IN	IN	IN	IN	IN	IN	IN	COM	COM	COM	COM	COM	COM	COM	
		+V	INT	1	2	3	4	5	6	COM	INT	1	1	1	1	1	
LOWER																	
UPPER	POWERFLEX 700H 20C-DA1-B	COM	IN	IN	IN	IN	IN	IN	IN	COM	COM	COM	COM	COM	COM	COM	
		COM	1	2	3	4	5	6	COM	COM	COM	COM	COM	COM	COM	COM	
LOWER																	
UPPER	POWERFLEX 700S	+V	IN	IN	IN	IN	IN	IN	IN	COM	COM	COM	COM	COM	COM	COM	
		+V	INT	1	2	3	4	5	6	COM	INT	1	2	1	2	3	
LOWER																	
UPPER	1794-IB8	+V	IN	IN	IN	IN	IN	IN	IN	IN	IN	IN	IN	IN	IN	COM	
		+V	0	1	2	3	4	5	6	7							
LOWER																	
UPPER	1794-IB16 1794-IV16	+V	IN	IN	IN	IN	IN	IN	IN	IN	IN	IN	IN	IN	IN	COM	
		+V	0	1	2	3	4	5	6	7							
LOWER																	
UPPER	1794-OB8	+V	OUT	OUT	OUT	OUT	OUT	OUT	OUT	OUT	OUT	OUT	OUT	OUT	OUT	COM	
		+V	0	1	2	3	4	5	6	7							
LOWER																	
UPPER	1794-OB8EP	+V	OUT	OUT	OUT	OUT	OUT	OUT	OUT	OUT	OUT	OUT	OUT	OUT	OUT	COM	
		+V	0	1	2	3	4	5	6	7							
LOWER																	
UPPER	1794-OW8	+V	OUT	OUT	OUT	OUT	OUT	OUT	OUT	OUT	OUT	OUT	OUT	OUT	OUT	COM	
		+V	0	0	1	1	2	2	3	3	4	4	5	5	6	7	
LOWER																	
UPPER	1794-IB10XOB6	+V	IN	IN	IN	IN	IN	IN	IN	IN	IN	IN	IN	IN	IN	COM	
		+V	0	1	2	3	4	5	6	7							
LOWER																	