

LEVEL		I/O CAT. NO.		16 RELAY/16 RELAY MASTER MODULE LABEL																																																	
LEFT	1746-OB16, OB16E OBP16	+V	+V	OUT 0	OUT 1	OUT 2	OUT 3	OUT 4	OUT 5	OUT 6	OUT 7	OUT 8	OUT 9	OUT 10	OUT 11	OUT 12	OUT 13	OUT 14	OUT 15	OUT 16	OUT 17	OUT 18	OUT 19	OUT 20	OUT 21	OUT 22	OUT 23	OUT 24	OUT 25	OUT 26																							
RIGHT	1746-OB16, OB16P	NC	COM	NO	NC	COM	NO	NC	COM	NO	NC	COM	NO	NC	COM	NO	NC	COM	NO	NC	COM	NO	NC	COM	NO	NC	COM	NO	NC	COM	NO																						
LEFT	1746-OB32, OB32E	+V	+V	OUT 0	OUT 1	OUT 2	OUT 3	OUT 4	OUT 5	OUT 6	OUT 7	OUT 8	OUT 9	OUT 10	OUT 11	OUT 12	OUT 13	OUT 14	OUT 15	OUT 16	OUT 17	OUT 18	OUT 19	OUT 20	OUT 21	OUT 22	OUT 23	OUT 24	OUT 25	OUT 26																							
RIGHT	1746-OB32, OB32P	NC	COM	NO	NC	COM	NO	NC	COM	NO	NC	COM	NO	NC	COM	NO	NC	COM	NO	NC	COM	NO	NC	COM	NO	NC	COM	NO	NC	COM	NO																						
LEFT	1746-OA16 1771-OAD, OBD	+V	+V	OUT 0	OUT 1	OUT 2	OUT 3	OUT 4	OUT 5	OUT 6	OUT 7	OUT 8	OUT 9	OUT 10	OUT 11	OUT 12	OUT 13	OUT 14	OUT 15	OUT 16	OUT 17	OUT 18	OUT 19	OUT 20	OUT 21	OUT 22	OUT 23	OUT 24	OUT 25	OUT 26																							
RIGHT	1746-OA16	NC	COM	NO	NC	COM	NO	NC	COM	NO	NC	COM	NO	NC	COM	NO	NC	COM	NO	NC	COM	NO	NC	COM	NO	NC	COM	NO	NC	COM	NO																						
LEFT	1756-OB16E, OA16 TC-ODD321, ODA161	+V	COM	OUT 0	OUT 1	OUT 2	OUT 3	OUT 4	OUT 5	OUT 6	OUT 7	OUT 8	OUT 9	OUT 10	OUT 11	OUT 12	OUT 13	OUT 14	OUT 15	OUT 16	OUT 17	OUT 18	OUT 19	OUT 20	OUT 21	OUT 22	OUT 23	OUT 24	OUT 25	OUT 26																							
RIGHT	1756-OB16E, OA16 TC-ODD321, ODA161	NC	COM	NO	NC	COM	NO	NC	COM	NO	NC	COM	NO	NC	COM	NO	NC	COM	NO	NC	COM	NO	NC	COM	NO	NC	COM	NO	NC	COM	NO																						
LEFT	1756-OB32 TC-ODD161	+V	+V	OUT 0	OUT 1	OUT 2	OUT 3	OUT 4	OUT 5	OUT 6	OUT 7	OUT 8	OUT 9	OUT 10	OUT 11	OUT 12	OUT 13	OUT 14	OUT 15	OUT 16	OUT 17	OUT 18	OUT 19	OUT 20	OUT 21	OUT 22	OUT 23	OUT 24	OUT 25	OUT 26																							
RIGHT	1756-OB32 TC-ODD161	NC	COM	NO	NC	COM	NO	NC	COM	NO	NC	COM	NO	NC	COM	NO	NC	COM	NO	NC	COM	NO	NC	COM	NO	NC	COM	NO	NC	COM	NO																						
	NUMERIC	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36	37	38	39	40	41	42	43	44	45	46	47	48	49	50	51	52

--- CUT AT 130mm ---