

LEVEL	I/O CAT. NO.	MODULE LABEL																
UPPER LEFT	1756-IA16I,IB16I, IH16I,IM16I TC-IDF16I,IDJ16I, IDK16I	+V	IN	+V	IN	+V	IN	+V	IN	+V	IN	+V	IN	+V	IN	+V	IN	
UPPER RIGHT		8F	8	9F	9	10F	10	11F	11	12F	12	13F	13	14F	14	15F	15	
LOWER LEFT		0	0	1	1	2	2	3	3	4	4	5	5	6	6	7	7	
LOWER RIGHT		8	8	9	9	10	10	11	11	12	12	13	13	14	14	15	15	
UPPER LEFT	1756-IB16D TC-IDX16I	+V	IN	+V	IN	+V	IN	+V	IN	+V	IN	+V	IN	+V	IN	+V	IN	
UPPER RIGHT		2F(A)	8	2F(B)	9	2F(C)	10	2F(D)	11	3F(A)	12	3F(B)	13	3F(C)	14	3F(D)	15	
LOWER LEFT		0	0	0	0	0	0	0	0	1	1	1	1	1	1	1	1	
LOWER RIGHT		2	2	2	2	2	2	2	2	3	3	3	3	3	3	3	3	
UPPER LEFT	1756-OA16I,OW16I TC-ODK16I, ORC16I	OUT	COM	OUT	COM	OUT	COM	OUT	COM	OUT	COM	OUT	COM	OUT	COM	OUT	COM	
UPPER RIGHT		8	8	9	9	10	10	11	11	12	12	13	13	14	14	15	15	
LOWER LEFT		0	0	0	0	1	1	2	2	3	3	4	4	5	5	6	6	
LOWER RIGHT		8	8	9	9	10	10	11	11	12	12	13	13	14	14	15	15	
UPPER LEFT	1756-OX8I TC-ORC08I	OUT	COM	OUT	COM	OUT	COM	OUT	COM	OUT	COM	OUT	COM	OUT	COM	OUT	COM	
UPPER RIGHT		4NC	4	4NO	4	5NC	5	5NO	5	6NC	6	6NO	6	7NC	7	7NO	7	
LOWER LEFT		0	0	0	0	1	1	1	1	2	2	2	2	3	3	3	3	
LOWER RIGHT		4	4	4	4	5	5	5	5	6	6	6	6	7	7	7	7	
UPPER LEFT	1771-ID16,IQ16	+V	IN	+V	IN	+V	IN	+V	IN	+V	IN	+V	IN	+V	IN	+V	IN	
UPPER RIGHT		10F	10	11F	11	12F	12	13F	13	14F	14	15F	15	16F	16	17F	17	
LOWER LEFT		0	0	1	1	2	2	3	3	4	4	5	5	6	6	7	7	
LOWER RIGHT		10	10	11	11	12	12	13	13	14	14	15	15	16	16	17	17	
UPPER LEFT	1771-OD16, -ODD	OUT	COM	OUT	COM	OUT	COM	OUT	COM	OUT	COM	OUT	COM	OUT	COM	OUT	COM	
UPPER RIGHT		10	10	11	11	12	12	13	13	14	14	15	15	16	16	17	17	
LOWER LEFT		0	0	1	1	2	2	3	3	4	4	5	5	6	6	7	7	
LOWER RIGHT		10	10	11	11	12	12	13	13	14	14	15	15	16	16	17	17	
	NUMERIC	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17
		18	19	20	21	22	23	24	25	26	27	28	29	30	31	32	33	34
		35	36	37	38	39	40	41	42	43	44	45	46	47	48	49	50	51
		52	53	54	55	56	57	58	59	60	61	62	63	64	65	66	67	68
		1	3	5	7	9	11	13	15	17	19	21	23	25	27	29	31	33
		2	4	6	8	10	12	14	16	18	20	22	24	26	28	30	32	34
		35	37	39	41	43	45	47	49	51	53	55	57	59	61	63	65	67
		36	38	40	42	44	46	48	50	52	54	56	58	60	62	64	66	68

--- CUT AT 85mm ---