

LEVEL	I/O CAT. NO.	MODULE LABEL																		
UPPER	1794-IB32	+V1	+V1	IN	IN	IN	IN	IN	IN	IN	IN	IN	IN	IN	IN	IN	IN	IN	COM	COM
		0	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	1	1	
LOWER		+V2									+V2									
UPPER		+V2	+V2	IN	IN	IN	IN	IN	IN	IN	IN	IN	IN	IN	IN	IN	IN	IN	COM	COM
		16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	2	2	
LOWER		+V2									+V2									
UPPER	1794-OB32P	+V1	+V1	OUT	OUT	OUT	OUT	OUT	OUT	OUT	OUT	OUT	OUT	OUT	OUT	OUT	OUT	OUT	COM	COM
		0	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	1	1	
LOWER		COM									COM									
UPPER		+V2	+V2	OUT	OUT	OUT	OUT	OUT	OUT	OUT	OUT	OUT	OUT	OUT	OUT	OUT	OUT	OUT	COM	COM
		16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	2	2	
LOWER		COM									COM									

NUMERIC	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36	37	38	39	40
	41	42	43	44	45	46	47	48	49	50	51	52	53	54	55	56	57	58	59	60
	61	62	63	64	65	66	67	68	69	70	71	72	73	74	75	76	77	78	79	80