

FICATIONS	RoHS, cULus, CSA, cURus???		
NUT MATERIAL	EPOXY-COATED ZINC		
VERMOLD MATERIAL	OIL RESISTANT PUR		
CT PLATING	GOLD OR GOLD FLASH OVER PALLADIUM-NICKEL		
CT MATERIAL	BRASS OR COPPER ALLOY		
BLE TYPE	PVC, 18AWG, 300V		
JACKET COLOR	GRAY		
RADIUS	IO X DIAMETER		
CONDUCTORS [AWG]	4 x I 8 AWG		
IELDING	UNSHIELDED		
E RATING	UL PLTC AWM STYLE 2661 VW-1 105C 300V, CSA AWM A/B 1/11 80C 300V FTI, UV OIL AND WATER RESISTANT		
PROTECTION	IP67 & IP69K		
	-20° $+105^{\circ}$ C $(-4^{\circ}$ $+221^{\circ}$ F)		
ATURE RATING	-20° +105°C (-4° +221°F)		
TURE RATING			

		Itomation		USED, COPIED OR DISCLOSED TO OTHERS, HE AUTHORIZED WRITTEN PERMISSION OF R AUTOMATION, INC.		
	889D-F4GEDM-*			Sheet I Of I		
			Size		Ver	
				889D-F4GEDM-*		
	Drawn by: LNT	Date: 12/20/2013			0.0	