

| 6                     | 7  | 8 |
|-----------------------|--|---|
| SPE                   | CIFICATIONS  |   |
| CERTIFICATIONS        | UL RECOGNIZED AND CSA CERTIFIED  |   |
| PLING NUT MATERIAL    | EPOXY-COATED ZINC  |   |
| FOR OVERMOLD MATERIAL | OIL RESISTANT PUR  |   |
| CONTACT PLATING       | GOLD OR GOLD FLASH OVER PALLADIUM-NICKEL   |   |
| ONTACT MATERIAL       | BRASS OR COPPER ALLOY  |   |
| CABLE TYPE            | TPE, 22AWG, 300V   |   |
| BLE JACKET COLOR      | YELLOW   |   |
| BEND RADIUS           | IO X DIAMETER  |   |
| OF CONDUCTORS [AWG]   | 4 x 2 2 A W G  |   |
| SHIELDING             | UNSHIELDED   |   |
| CABLE RATING          | UL AWM STYLE 20328 600V VW-I 105C TO -50C WATER<br>RESISTANT, CSA AWM I/II A/B 105C 600V FT2 |   |
| GRESS PROTECTION      | NEMA 6P, I200 PSI (8270 kPa) WASHDOWN, IP69K   |   |
| IPERATURE RATING      | -50° +105°C (-58° +221°F)  |   |

| DIMENSIONS & INFORMATION SHOWN ARE<br>FOR LATEST UPDATE PLEASE REFER h++ |  |  |
|--|--|--|
| Rockwell<br>Automation   | CONFIDENTIAL AND PROPRIETARY INFORMATION.<br>THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY<br>INFORMATION OF ROCKWELL AUTOMATION, INC. AND MAY<br>NOT BE USED, COPIED OR DISCLOSED TO OTHERS, EXCEPT<br>WITH THE AUTHORIZED WRITTEN PERMISSION OF ROCKWELL<br>AUTOMATION, INC. |  |
| 889D-F4HC-*  | Sheet   Of  <br>size 889D-F4HC-* 0.0   |  |
| Drawn by: LNT Date: 11/14/2013   |  |  |