




	1	2	3	4	5	6	7	8						
	MALE END VIEW		FEMALE END VIEW		SPECIFICATIONS									
A					CERTIFICATIONS		UL RECOGNIZED AND CSA CERTIFIED							
					COUPLING NUT MATERIAL		DC MICRO: BLACK EPOXY-COATED ZINC, PICO: NICKEL-PLATED BRASS							
B					CONNECTOR OVERMOLD MATERIAL		DC MICRO: MOLDED OIL-RESISTANT PUR, PICO: MOLDED OIL-RESISTANT TPE							
					CONTACT PLATING		GOLD OVER NICKEL-PLATED BRASS							
					CONTACT MATERIAL		BRASS OR COPPER ALLOY							
					CABLE TYPE		PUR, 24AWG, 300V							
					CABLE JACKET COLOR		BLACK							
					BEND RADIUS		10 X DIAMETER							
					NUMBER OF CONDUCTORS [AWG]		3X24 AWG (PICO MALE), 4X24 AWG (MICRO FEMALE)							
C					SHIELDING		UNSHIELD HALOGEN-FREE							
					CABLE RATING		UL AWM STYLE 20233, 21198 OR 10493 80°C 300V FT2							
					INGRESS PROTECTION		IP67							
					TEMPERATURE RATING		-20°...+80°C (-4°...+176°F)							
D														
E														
F														
G														
	DIMENSIONS & INFORMATION SHOWN ARE FOR REFERENCE ONLY AND FOR LATEST UPDATE PLEASE REFER http://www.ab.com/catalogs/													
H							CONFIDENTIAL AND PROPRIETARY INFORMATION. THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION OF ROCKWELL AUTOMATION, INC. AND MAY NOT BE USED, COPIED OR DISCLOSED TO OTHERS, EXCEPT WITH THE AUTHORIZED WRITTEN PERMISSION OF ROCKWELL AUTOMATION, INC.							
							Sheet 1 Of 1							
							Size	Ver						
	889D-F4JBP3M-*						C	889D-F4JBP3M-*	0.0					
	Drawn by: LNT			Date: 05-15-2015										
	NOTES: 1. (*) REPRESENTS THE CABLE LENGTH IN METERS. 2. ALL DIMENSIONS ARE IN MM [INCHES] UNLESS AND OTHERWISE SPECIFIED.													