




	1	2	3	4	5	6	7	8	
	MALE END VIEW		FEMALE END VIEW		SPECIFICATIONS				
A					CERTIFICATIONS		UL RECOGNIZED AND CSA CERTIFIED		
					COUPLING NUT MATERIAL		NICKEL-PLATED BRASS		
					CONNECTOR OVERMOLD MATERIAL		OIL-RESISTANT PUR		
					CONTACT PLATING		GOLD OVER NICKEL-PLATED BRASS		
					CONTACT MATERIAL		BRASS OR COPPER ALLOY		
B					CABLE TYPE		PUR, 18/22 AWG, 300V		
					CABLE JACKET COLOR		BLACK		
					BEND RADIUS		10 X DIAMETER		
					NUMBER OF CONDUCTORS [AWG]		3X18/16X22 AWG (M23 MALE), 3X18/16X22 AWG (M23 FEMALE)		
C					SHIELDING		UNSHIELDED		
					CABLE RATING		300V		
					INGRESS PROTECTION		IP67, IP68		
					TEMPERATURE RATING		-20°...+105°C (-4°...+221°F)		
D									
E									
F									
G									
H	NOTES: 1. (*) REPRESENTS THE CABLE LENGTH IN METERS. 2. ALL DIMENSIONS ARE IN MM [INCHES] UNLESS AND OTHERWISE SPECIFIED.					DIMENSIONS & INFORMATION SHOWN ARE FOR REFERENCE ONLY AND FOR LATEST UPDATE PLEASE REFER http://www.ab.com/catalogs/			
						Rockwell Automation		CONFIDENTIAL AND PROPRIETARY INFORMATION. THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION OF ROCKWELL AUTOMATION, INC. AND MAY NOT BE USED, COPIED OR DISCLOSED TO OTHERS, EXCEPT WITH THE AUTHORIZED WRITTEN PERMISSION OF ROCKWELL AUTOMATION, INC.	
						889M-F19RMMM-*		Sheet 1 Of 1	
						Drawn by: LNT	Date: 06-10-2015	SizeC 889M-F19RMMM-* Ver0.0	