






	1	2	3	4	5	6	7	8
	RIGHT ANGLE MALE END VIEW		RIGHT ANGLE FEMALE END VIEW		SPECIFICATIONS			
A					CERTIFICATIONS		UL RECOGNIZED AND CSA CERTIFIED	
					COUPLING NUT MATERIAL		NICKEL-PLATED BRASS	
B					CONNECTOR OVERMOLD MATERIAL		OIL-RESISTANT PUR	
					CONTACT PLATING		GOLD OVER NICKEL-PLATED BRASS	
C					CONTACT MATERIAL		BRASS OR COPPER ALLOY	
					CABLE TYPE		PUR, 18/22AWG, 300V	
					CABLE JACKET COLOR		BLACK	
					BEND RADIUS		10 X DIAMETER	
					NUMBER OF CONDUCTORS [AWG]		3X18/8X22 AWG (M23 MALE), 3X18/8X22 AWG (M23 FEMALE)	
					SHIELDING		UNSHIELDED	
					CABLE RATING		300V	
					INGRESS PROTECTION		IP67, IP68	
TEMPERATURE RATING		-20°...+105°C (-4°...+221°F)						
	11-PIN, M23 X 1 RIGHT ANGLE MALE CONNECTOR		11-PIN, M23 X 1 RIGHT ANGLE FEMALE CONNECTOR					



DIMENSIONS & INFORMATION SHOWN ARE FOR REFERENCE ONLY AND FOR LATEST UPDATE PLEASE REFER <http://www.ab.com/catalogs/>

		CONFIDENTIAL AND PROPRIETARY INFORMATION. THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION OF ROCKWELL AUTOMATION, INC. AND MAY NOT BE USED, COPIED OR DISCLOSED TO OTHERS, EXCEPT WITH THE AUTHORIZED WRITTEN PERMISSION OF ROCKWELL AUTOMATION, INC.	
		Sheet 1 Of 1	
889M-R1IRMME-*		Size	Ver
Drawn by: LNT	Date: 06-10-2015	C	889M-R1IRMME-* 0.0

NOTES:
1. (*) REPRESENTS THE CABLE LENGTH IN METERS.
2. ALL DIMENSIONS ARE IN MM [INCHES] UNLESS AND OTHERWISE SPECIFIED.