








	1	2	3	4	5	6	7	8
	MALE END VIEW		RIGHT ANGLE FEMALE END VIEW		SPECIFICATIONS			
A					CERTIFICATIONS	UL RECOGNIZED AND CSA CERTIFIED		
					COUPLING NUT MATERIAL	NICKEL-PLATED BRASS		
					CONNECTOR OVERMOLD MATERIAL	OIL-RESISTANT PUR		
					CONTACT PLATING	GOLD OVER NICKEL-PLATED BRASS		
B					CONTACT MATERIAL	BRASS OR COPPER ALLOY		
					CABLE TYPE	PVC, 18AWG WITH ONE TWISTED PAIR, 300V		
					CABLE JACKET COLOR	YELLOW		
					BEND RADIUS	10 X DIAMETER		
C					NUMBER OF CONDUCTORS [AWG]	12X18 AWG (M23 MALE), 12X18 AWG (M23 FEMALE)		
					SHIELDING	UNSHIELDED		
					CABLE RATING	300V		
					INGRESS PROTECTION	IP67, IP68		
	12-PIN, M23 X 1 STRAIGHT MALE CONNECTOR		12-PIN, M23 X 1 RIGHT ANGLE FEMALE CONNECTOR		TEMPERATURE RATING	-20°...+105°C (-4°...+221°F)		



H	NOTES: 1. (*) REPRESENTS THE CABLE LENGTH IN METERS. 2. ALL DIMENSIONS ARE IN MM [INCHES] UNLESS AND OTHERWISE SPECIFIED.	DIMENSIONS & INFORMATION SHOWN ARE FOR REFERENCE ONLY AND FOR LATEST UPDATE PLEASE REFER http://www.ab.com/catalogs/			
		Rockwell Automation		CONFIDENTIAL AND PROPRIETARY INFORMATION. THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION OF ROCKWELL AUTOMATION, INC. AND MAY NOT BE USED, COPIED OR DISCLOSED TO OTHERS, EXCEPT WITH THE AUTHORIZED WRITTEN PERMISSION OF ROCKWELL AUTOMATION, INC.	
		889M-R12AHMM-*		Sheet 1 Of 1	
		Drawn by: LNT	Date: 06-10-2015	C	889M-R12AHMM-* Ver 0.0