

	1	2	3	4	5	6	7	8
	RIGHT ANGLE MALE END VIEW		RIGHT ANGLE FEMALE END VIEW		SPECIFICATIONS			
A					CERTIFICATIONS		UL RECOGNIZED AND CSA CERTIFIED	
					COUPLING NUT MATERIAL		NICKEL-PLATED BRASS	
					CONNECTOR OVERMOLD MATERIAL		OIL-RESISTANT PUR	
					CONTACT PLATING		GOLD OVER NICKEL-PLATED BRASS	
					CONTACT MATERIAL		BRASS OR COPPER ALLOY	
B					CABLE TYPE		PUR, 18/22 AWG, 300V	
					CABLE JACKET COLOR		BLACK	
					BEND RADIUS		10 X DIAMETER	
					NUMBER OF CONDUCTORS [AWG]		3X18/16X22 AWG (M23 MALE), 3X18/16X22 AWG (M23 FEMALE)	
					SHIELDING		UNSHIELDED	
					CABLE RATING		300V	
					INGRESS PROTECTION		IP67, IP68	
C					TEMPERATURE RATING		-20°...+105°C (-4°...+221°F)	
	19-PIN, M23 X 1 RIGHT ANGLE MALE CONNECTOR		19-PIN, M23 X 1 RIGHT ANGLE FEMALE CONNECTOR					

