


	1	2	3	4	5	6	7	8
	MALE END VIEW		RIGHT ANGLE FEMALE END VIEW		SPECIFICATIONS			
A					CERTIFICATIONS		UL RECOGNIZED AND CSA CERTIFIED	
					COUPLING NUT MATERIAL		NICKEL-PLATED BRASS	
B					CONNECTOR OVERMOLD MATERIAL		OIL-RESISTANT PUR	
					CONTACT PLATING		GOLD OVER NICKEL-PLATED BRASS	
C					CONTACT MATERIAL		BRASS OR COPPER ALLOY	
					CABLE TYPE		PUR, 18/22 AWG, 300V	
					CABLE JACKET COLOR		BLACK	
BEND RADIUS					10 X DIAMETER			
					NUMBER OF CONDUCTORS [AWG]		3X18/16X22 AWG (M23 MALE), 3X18/16X22 AWG (M23 FEMALE)	
SHIELDING					UNSHIELDED			
					CABLE RATING		300V	
INGRESS PROTECTION					IP67, IP68			
					TEMPERATURE RATING		-20°...+105°C (-4°...+221°F)	
	19-PIN, M23 X 1 STRAIGHT MALE CONNECTOR		19-PIN, M23 X 1 RIGHT ANGLE FEMALE CONNECTOR					



DIMENSIONS & INFORMATION SHOWN ARE FOR REFERENCE ONLY AND FOR LATEST UPDATE PLEASE REFER <http://www.ab.com/catalogs/>

		CONFIDENTIAL AND PROPRIETARY INFORMATION. THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION OF ROCKWELL AUTOMATION, INC. AND MAY NOT BE USED, COPIED OR DISCLOSED TO OTHERS, EXCEPT WITH THE AUTHORIZED WRITTEN PERMISSION OF ROCKWELL AUTOMATION, INC.	
		Sheet 1 Of 1	
889M-R19RMMU-*		Size	Ver
Drawn by: LNT	Date: 06-09-2015	C	889M-R19RMMU-* 0.0

NOTES:
1. (*) REPRESENTS THE CABLE LENGTH IN METERS.
2. ALL DIMENSIONS ARE IN MM [INCHES] UNLESS AND OTHERWISE SPECIFIED.