


	1	2	3	4	5	6	7	8
	MALE END VIEW		FEMALE END VIEW		SPECIFICATIONS			
A	<p>1-GREEN (LONG PIN) 2-BLACK 3-WHITE 3-PIN, 7/8-16UN 2B STRAIGHT MALE CONNECTOR</p>		<p>1-GREEN 2-BLACK 3-WHITE 3-PIN, 7/8-16UN 2B STRAIGHT FEMALE CONNECTOR</p>		CERTIFICATIONS		UL RECOGNIZED AND CSA CERTIFIED	
B					COUPLING NUT MATERIAL		EPOXY-COATED ZINC	
C					CONNECTOR OVERMOLD MATERIAL		OIL RESISTANT TPE	
D					CONTACT PLATING		GOLD OR GOLD FLASH OVER PALLADIUM-NICKEL	
E					CONTACT MATERIAL		BRASS OR COPPER ALLOY	
F					CABLE TYPE		TPE, 18AWG, 300V	
G					CABLE JACKET COLOR		YELLOW	
H					BEND RADIUS		10 X DIAMETER	
					NUMBER OF CONDUCTORS [AWG]		3x18 AWG	
					FLEX RATING		5 MILLION CYCLES (BASED ON 10 TIMES CABLE OD)	
					SHIELDING		UNSHIELDED	
					CABLE RATING		UL AWM STYLE 20327 VW-1 105C 300V, CSA AWM A/B 1/II 105C 300V FTI, UV OIL AND WATER RESISTANT	
					INGRESS PROTECTION		NEMA 4, 6P, 12, 13; IP67; 1200 PSI WASHDOWN, IP69K	
					TEMPERATURE RATING		-50° ... +105°C (-58° ... +221°F)	



DIMENSIONS & INFORMATION SHOWN ARE FOR REFERENCE ONLY AND FOR LATEST UPDATE PLEASE REFER <http://www.ab.com/catalogs/>

NOTES:  
1. (\*) REPRESENTS THE CABLE LENGTH IN METERS.  
2. ALL DIMENSIONS ARE IN MM [INCHES] UNLESS AND OTHERWISE SPECIFIED.

		CONFIDENTIAL AND PROPRIETARY INFORMATION. THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION OF ROCKWELL AUTOMATION, INC. AND MAY NOT BE USED, COPIED OR DISCLOSED TO OTHERS, EXCEPT WITH THE AUTHORIZED WRITTEN PERMISSION OF ROCKWELL AUTOMATION, INC.	
		Sheet 1 Of 1	
889N-F3HJNU-*		Size	Ver
C		889N-F3HJNU-*	0.0
Drawn by: LNT	Date: 03/10/2014		