




RIGHT ANGLE FEMALE END VIEW

MALE END VIEW

SPECIFICATIONS

CERTIFICATIONS

UL RECOGNIZED AND CSA CERTIFIED

COUPLING NUT MATERIAL

EPOXY-COATED ZINC

CONNECTOR OVERMOLD MATERIAL

OIL RESISTANT TPE

CONTACT PLATING

GOLD OR GOLD FLASH OVER PALLADIUM-NICKEL

CONTACT MATERIAL

BRASS OR COPPER ALLOY

CABLE TYPE

CPE, 18AWG, 300V

CABLE JACKET COLOR

YELLOW

BEND RADIUS

10 X DIAMETER

NUMBER OF CONDUCTORS [AWG]

3x18 AWG

SHIELDING

UNSHIELDED

CABLE RATING




UL SJ00W 105C 300V WATER RESISTANT, CSA -50C FT-1 300V

INGRESS PROTECTION

NEMA 4, 6P, 12, 13; IP67; 1200 PSI WASHDOWN, IP69K

TEMPERATURE RATING

-50°... +105°C (-58°... +221°F)



*METER
SEE NOTE 1

DIMENSIONS & INFORMATION SHOWN ARE FOR REFERENCE ONLY AND FOR LATEST UPDATE PLEASE REFER <http://www.ab.com/catalogs/>

**Rockwell
Automation**

CONFIDENTIAL AND PROPRIETARY INFORMATION.
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY
INFORMATION OF ROCKWELL AUTOMATION, INC. AND MAY
NOT BE USED, COPIED OR DISCLOSED TO OTHERS, EXCEPT
WITH THE AUTHORIZED WRITTEN PERMISSION OF ROCKWELL
AUTOMATION, INC.

889N-R3WENU-*

Sheet 1 Of 1

Size Ver
C 889N-R3WENU-* 0.0

Drawn by: LNT Date: 03/10/2014

NOTES:
1. (*) REPRESENTS THE CABLE LENGTH IN METERS.
2. ALL DIMENSIONS ARE IN MM [INCHES] UNLESS AND OTHERWISE SPECIFIED.