




RIGHT ANGLE FEMALE END VIEW

MALE END VIEW

SPECIFICATIONS

CERTIFICATIONS

UL RECOGNIZED AND CSA CERTIFIED

COUPLING NUT MATERIAL

EPOXY-COATED ZINC

CONNECTOR OVERMOLD MATERIAL

OIL RESISTANT TPE

CONTACT PLATING

GOLD OR GOLD FLASH OVER PALLADIUM-NICKEL

CONTACT MATERIAL

BRASS OR COPPER ALLOY

CABLE TYPE

PVC, 18AWG, 300V

CABLE JACKET COLOR

YELLOW

BEND RADIUS

10 X DIAMETER

NUMBER OF CONDUCTORS [AWG]

4x18 AWG

SHIELDING

UNSHIELDED

CABLE RATING



UL AWM STYLE 2661 VW-1 105C 300V, CSA AWM A/B 1/11 80C 300V FT1, UV OIL AND WATER RESISTANT

INGRESS PROTECTION

NEMA 4, 6P, 12, 13; IP67; 1200 PSI WASHDOWN, IP69K


TEMPERATURE RATING

-20°... +105°C (-4°... +221°F)



4-PIN, 7/8-16UN 2B
RIGHT ANGLE FEMALE CONNECTOR

4-PIN, 7/8-16UN 2B
STRAIGHT MALE CONNECTOR



*METER
SEE NOTE 1

DIMENSIONS & INFORMATION SHOWN ARE FOR REFERENCE ONLY AND
FOR LATEST UPDATE PLEASE REFER <http://www.ab.com/catalogs/>

**Rockwell
Automation**

CONFIDENTIAL AND PROPRIETARY INFORMATION.
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY
INFORMATION OF ROCKWELL AUTOMATION, INC. AND MAY
NOT BE USED, COPIED OR DISCLOSED TO OTHERS, EXCEPT
WITH THE AUTHORIZED WRITTEN PERMISSION OF ROCKWELL
AUTOMATION, INC.

Sheet 1 Of 1

889N-R4AENU-*

Size Ver
C 889N-R4AENU-* 0.0

Drawn by: LNT

Date: 03/10/2014

NOTES:
1. (*) REPRESENTS THE CABLE LENGTH IN METERS.
2. ALL DIMENSIONS ARE IN MM [INCHES] UNLESS AND OTHERWISE SPECIFIED.