




RIGHT ANGLE FEMALE END VIEW

RIGHT ANGLE MALE END VIEW

4-WHITE 1-BLACK

1-BLACK 4-WHITE (LONG PIN)

3-BROWN 2-BLUE

2-BLUE 3-BROWN

4-PIN, 7/8-16UN 2B
RIGHT ANGLE FEMALE CONNECTOR

4-PIN, 7/8-16UN 2B
RIGHT ANGLE MALE CONNECTOR

SPECIFICATIONS

CERTIFICATIONS

UL RECOGNIZED AND CSA CERTIFIED

COUPLING NUT MATERIAL

EPOXY-COATED ZINC

CONNECTOR OVERMOLD MATERIAL

OIL RESISTANT TPE

CONTACT PLATING

GOLD OR GOLD FLASH OVER PALLADIUM-NICKEL

CONTACT MATERIAL

BRASS OR COPPER ALLOY

CABLE TYPE

PVC, 18AWG, 300V

CABLE JACKET COLOR

YELLOW

BEND RADIUS

10 X DIAMETER

NUMBER OF CONDUCTORS [AWG]

4x18 AWG

SHIELDING

UNSHIELDED

CABLE RATING

UL AWM STYLE 2661 VW-1 105C 300V, CSA AWM A/B 1/1 80C 300V FT1, UV OIL AND WATER RESISTANT

INGRESS PROTECTION

NEMA 4, 6P, 12, 13; IP67; 1200 PSI WASHDOWN, IP69K

TEMPERATURE RATING

-20°... +105°C (-4°... +221°F)

NOTES:
1. (*) REPRESENTS THE CABLE LENGTH IN METERS.
2. ALL DIMENSIONS ARE IN MM [INCHES] UNLESS AND OTHERWISE SPECIFIED.

Rockwell Automation

889N-R4AENV-*

Drawn by: LNT

Date: 03/10/2014

CONFIDENTIAL AND PROPRIETARY INFORMATION. THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION OF ROCKWELL AUTOMATION, INC. AND MAY NOT BE USED, COPIED OR DISCLOSED TO OTHERS, EXCEPT WITH THE AUTHORIZED WRITTEN PERMISSION OF ROCKWELL AUTOMATION, INC.

Sheet 1 Of 1

Size

C

889N-R4AENV-*

Ver

0.0