




RIGHT ANGLE FEMALE END VIEW

MALE END VIEW

SPECIFICATIONS

CERTIFICATIONS

UL RECOGNIZED AND CSA CERTIFIED

COUPLING NUT MATERIAL

EPOXY-COATED ZINC

CONNECTOR OVERMOLD MATERIAL

OIL RESISTANT TPE

CONTACT PLATING

GOLD OR GOLD FLASH OVER PALLADIUM-NICKEL

CONTACT MATERIAL

BRASS OR COPPER ALLOY

CABLE TYPE

PVC, 16AWG, 600V

CABLE JACKET COLOR

YELLOW

BEND RADIUS

10 X DIAMETER

NUMBER OF CONDUCTORS [AWG]

6x16 AWG

SHIELDING

UNSHIELDED

CABLE RATING


UL STOOW VW-1 105C 600V, CSA ST 105C 600V FT2, UV OIL AND WATER RESISTANT

INGRESS PROTECTION


NEMA 4, 6P, 12, 13; IP67; 1200 PSI WASHDOWN, IP69K

TEMPERATURE RATING


-20°... +105°C (-4°... +221°F)



6-PIN, 7/8-16UN 2B RIGHT ANGLE FEMALE CONNECTOR



6-PIN, 7/8-16UN 2B STRAIGHT MALE CONNECTOR



*METER
SEE NOTE 1

DIMENSIONS & INFORMATION SHOWN ARE FOR REFERENCE ONLY AND FOR LATEST UPDATE PLEASE REFER <http://www.ab.com/catalogs/>

Rockwell Automation

CONFIDENTIAL AND PROPRIETARY INFORMATION. THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION OF ROCKWELL AUTOMATION, INC. AND MAY NOT BE USED, COPIED OR DISCLOSED TO OTHERS, EXCEPT WITH THE AUTHORIZED WRITTEN PERMISSION OF ROCKWELL AUTOMATION, INC.

Sheet 1 Of 1

889N-R6AFNU-*

Size Ver
C 889N-R6AFNU-* 0.0

Drawn by: LNT Date: 03/10/2014

- NOTES:
1. (*) REPRESENTS THE CABLE LENGTH IN METERS.
2. ALL DIMENSIONS ARE IN MM [INCHES] UNLESS AND OTHERWISE SPECIFIED.