


| MALE END VIEW | FEMALE END VIEW |
|---|---|
|  |  |
| 3-PIN, M8 X 1<br>STRAIGHT MALE CONNECTOR | 3-PIN, M8 X 1<br>STRAIGHT FEMALE CONNECTOR |

## SPECIFICATIONS

| | |
|---|---|
| CERTIFICATIONS | UL RECOGNIZED AND CSA CERTIFIED |
| COUPLING NUT MATERIAL | NICKEL PLATED BRASS |
| CONNECTOR OVERMOLD MATERIAL | OIL RESISTANT PUR |
| CONTACT PLATING | GOLD OVER NICKEL-PLATED BRASS |
| CONTACT MATERIAL | BRASS OR COPPER ALLOY |
| CABLE TYPE | PVC, 24AWG, 300V |
| CABLE JACKET COLOR | YELLOW |
| BEND RADIUS | 10 X DIAMETER |
| NUMBER OF CONDUCTORS [AWG] | 3X24 AWG (PICO MALE), 3X24 AWG (PICO FEMALE) |
| SHIELDING | UNSHIELDED |
| CABLE RATING | UL CM AWM STYLE 2661 VW-1 105°C 300V, CSA AWM A/B 1/11 105°C 300V FT1 |
| INGRESS PROTECTION | IP67 |
| TEMPERATURE RATING | -20°... +105°C (-4°... +221°F) |




DIMENSIONS & INFORMATION SHOWN ARE FOR REFERENCE ONLY AND FOR LATEST UPDATE PLEASE REFER http://www.ab.com/catalogs/

NOTES:
1. (*) REPRESENTS THE CABLE LENGTH IN METERS.
2. ALL DIMENSIONS ARE IN MM [INCHES] UNLESS AND OTHERWISE SPECIFIED.

Rockwell Automation

CONFIDENTIAL AND PROPRIETARY INFORMATION.
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION OF ROCKWELL AUTOMATION, INC. AND MAY NOT BE USED, COPIED OR DISCLOSED TO OTHERS, EXCEPT WITH THE AUTHORIZED WRITTEN PERMISSION OF ROCKWELL AUTOMATION, INC.

889P-A3ABPM-*

Sheet 1 Of 1

Drawn by: LNT | Date: 04-09-2015

Size: C | 889P-A3ABPM-* | Ver: 0.0