



	1	2	3	4	5	6	7	8
	MALE END VIEW		RIGHT ANGLE FEMALE END VIEW		SPECIFICATIONS			
A	<p>4-BLACK</p> <p>1-BROWN</p> <p>3-BLUE</p> <p>3-PIN, M8 X 1 STRAIGHT MALE CONNECTOR</p>		<p>4-BLACK</p> <p>3-BLUE</p> <p>1-BROWN</p> <p>3-PIN, M8 X 1 RIGHT ANGLE FEMALE CONNECTOR</p>		CERTIFICATIONS		UL RECOGNIZED AND CSA CERTIFIED	
					COUPLING NUT MATERIAL		NICKEL-PLATED BRASS	
B					CONNECTOR OVERMOLD MATERIAL		OIL-RESISTANT PUR	
					CONTACT PLATING		GOLD OVER NICKEL-PLATED BRASS	
C					CONTACT MATERIAL		BRASS OR COPPER ALLOY	
					CABLE TYPE		PVC, 24AWG, 300V	
					CABLE JACKET COLOR		YELLOW	
					BEND RADIUS		10 X DIAMETER	
					NUMBER OF CONDUCTORS [AWG]		3X24 AWG (PICO MALE), 3X24 AWG (PICO FEMALE)	
					SHIELDING		UNSHIELDED	
					CABLE RATING		UL CM AWM STYLE 2661 VW-1 105°C 300V, CSA AWM A/B 1/II 105°C 300V FTI	
					INGRESS PROTECTION		IP67	
					TEMPERATURE RATING		-20° ... +105°C (-4° ... +221°F)	



DIMENSIONS & INFORMATION SHOWN ARE FOR REFERENCE ONLY AND FOR LATEST UPDATE PLEASE REFER <http://www.ab.com/catalogs/>

		CONFIDENTIAL AND PROPRIETARY INFORMATION. THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION OF ROCKWELL AUTOMATION, INC. AND MAY NOT BE USED, COPIED OR DISCLOSED TO OTHERS, EXCEPT WITH THE AUTHORIZED WRITTEN PERMISSION OF ROCKWELL AUTOMATION, INC.	
		Sheet 1 Of 1	
889P-P3ABPM-*		Size	Ver
Drawn by: LNT		C	889P-P3ABPM-* 0.0
Date: 04-16-2015			

NOTES:
1. (*) REPRESENTS THE CABLE LENGTH IN METERS.
2. ALL DIMENSIONS ARE IN MM [INCHES] UNLESS AND OTHERWISE SPECIFIED.