


1		2		3		4		5		6		7		8					
FEMALE END VIEW				SPECIFICATIONS															
												CERTIFICATIONS				UL RECOGNIZED AND CSA CERTIFIED			
												COUPLING NUT MATERIAL				EPOXY-COATED ZINC			
												CONNECTOR OVERMOLD MATERIAL				OIL RESISTANT PVC			
												CONTACT PLATING				GOLD OR GOLD FLASH OVER PALLADIUM-NICKEL			
												CONTACT MATERIAL				BRASS OR COPPER ALLOY			
												CABLE TYPE				TPE, 18AWG, 300V			
												CABLE JACKET COLOR				YELLOW			
												BEND RADIUS				10 X DIAMETER			
												NUMBER OF CONDUCTORS [AWG]				3x18 AWG			
												SHIELDING				UNSHIELDED			
												FLEX RATING				5 MILLION CYCLES (BASED ON 10 TIMES CABLE OD)			
				CABLE RATING				UL AWM, UV, OIL AND WATER RESISTANT, 18 AWG											
				INGRESS PROTECTION				IP67, IP69K											
				TEMPERATURE RATING				-50°... +105°C (-58°... +221°F)											



NOTES:
 1. (*) REPRESENTS THE CABLE LENGTH IN METERS.
 2. ALL DIMENSIONS ARE IN MM [INCHES] UNLESS AND OTHERWISE SPECIFIED.

DIMENSIONS & INFORMATION SHOWN ARE FOR REFERENCE ONLY AND FOR LATEST UPDATE PLEASE REFER <http://www.ab.com/catalogs/>

Rockwell Automation		<small>CONFIDENTIAL AND PROPRIETARY INFORMATION. THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION OF ROCKWELL AUTOMATION, INC. AND MAY NOT BE USED, COPIED OR DISCLOSED TO OTHERS, EXCEPT WITH THE AUTHORIZED WRITTEN PERMISSION OF ROCKWELL AUTOMATION, INC.</small>	
		Sheet 1 Of 1	
889R-F3HJA-*		Size	Ver
Drawn by: LNT		Date: 04/28/2014	C 889R-F3HJA-* 0.0