



FRONT VIEW



INSIDE VIEW

DOOR NOT SHOWN FOR CLARITY



REV.	DATE	BY	ECN/CR. NO.
A	2/3/06	REH	
B	8/3/06	JCL	
C	11/15/06	REH	
D	12/21/06	REH	
E	7/8/08	ALB	

DR.	BY REH/ACI	CHK.	BY JCL/ACI	ENG.	JFH/ACI	DWG.	95D01559 -	NEXT SH.	1	SH. IND.	1
DATE	11/18/05	DATE	02/17/06	DATE	11/18/05	NO.					

DATE	BY	APPROVAL
		DESIGN REVIEW
		FDR MANUFACTURING
		AS SHIPPED
		AS COMMISSIONED

01  
02  
03  
04  
05  
06  
07  
08  
09  
10  
11  
12  
13  
14  
15  
16  
17  
18  
19  
20  
21  
22  
23  
24  
25  
26  
27  
28  
29  
30  
31  
32  
33  
34  
35  
36  
37  
38  
39  
40  
41  
42

INPUT POWER  
TERMINAL BLOCK

OPTIONAL  
CIRCUIT BREAKER  
CB1

**Rockwell  
Automation**

THIS DRAWING IS THE PROPERTY OF ROCKWELL AUTOMATION, INC.  
OR ITS SUBSIDIARIES AND MAY NOT BE COPIED, USED OR DISCLOSED FOR ANY  
PURPOSE EXCEPT AS AUTHORIZED IN WRITING BY ROCKWELL AUTOMATION, INC.  
TITLE  
LAYOUT DRAWING  
PF400, FRAME D, STYLE B, 15-30HP @ 208VAC, 25-40HP @ 480VAC  
NEMA 3R

01  
02  
03  
04  
05  
06  
07  
08  
09  
10  
11  
12  
13  
14  
15  
16  
17  
18  
19  
20  
21  
22  
23  
24  
25  
26  
27  
28  
29  
30  
31  
32  
33  
34  
35  
36  
37  
38  
39  
40  
41  
42