

Circuit Protection Design and SCCR Tables-ArmorStart

Bulletin Number	Protective Device	Control Power	3 Phase Inputs					
			200V 50/60Hz	230V 50/60Hz	380V 50/60Hz	480V 50/60Hz	480Y 50/60Hz	600V 50Hz
ArmorStart Classic, 280 Full Voltage Starter/281 Reversing Starter	AB 140U Molded Case Circuit Breaker	Conduit Entrance	280_281_200V-CR	280_281_230V-CR		280_281_480V-CR		
		Round Media	280_281_200V-RR	280_281_230V-RR		280_281_480V-RR		
Conduit Entrance			284_230V-CR	284_380V-CR	284_480V-CR			
Round Media			284_230V-RR	284_380V-RR	284_480V-RR			
Conduit Entrance						290_291_480YV-CR		
Round Media						290_291_480YV-RR		
Conduit Entrance						294_480YV-CR		
Round Media						294_480YV-RR		
ArmorStart Classic, 280 Full Voltage Starter/281 Reversing Starter	UL Class T Fuse	Conduit Entrance	280_281_200V-CR	280_281_230V-CR		280_281_480V-CR		280_281_600V-CR
Round Media		280_281_200V-RR	280_281_230V-RR		280_281_480V-RR		280_281_600V-RR	
Conduit Entrance			284_230V-CR	284_380V-CR	284_480V-CR		284_600V-CR	
Round Media			284_230V-RR	284_380V-RR	284_480V-RR		284_600V-RR	
Conduit Entrance						290_291_480YV-CR		
Round Media						290_291_480YV-RR		
Conduit Entrance						294_480YV-CR		
Round Media						294_480YV-RR		