







IP54 TYPE 12



- NOTES:
- ENCLOSURE SYSTEM IS 2000MM TALL 600MM DEEP
 - DRIVE SIZE SHOWN:


INPUT VOLTAGE	NORMAL DUTY RATING
400	160...400 kW
480	250...650 HP
600	250...550 HP
690	200...500 kW



DETAIL A

DIMENSIONS IN MM
UNLESS OTHERWISE SPECIFIED:
DIMENSIONS & TOLERANCING IN ACCORDANCE
WITH ASME Y14.5-2009
ALL UNTOLERANCED DIMENSIONS ARE BASIC
AND CONTROLLED BY THE CAD MODEL AND
CONTROLLED SIMULTANEOUSLY.

		CONFIDENTIAL AND PROPRIETARY INFORMATION THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION OF ROCKWELL AUTOMATION, INC. AND MAY NOT BE USED, COPIED OR DISCLOSED TO OTHERS, EXCEPT WITH THE AUTHORIZED WRITTEN PERMISSION OF ROCKWELL AUTOMATION, INC.	
STANDARD PF755TL TR FRAME-8		DATE: 2021-08-16	SHEET 1 OF 2
DESCRIPTION	SIZE D1R	D	VER
CREATED BY: TPS1	CHANGED BY:	10006321536	00



STANDARD PF755TL TR FRAME-8

CREATED BY:TPS1 CHANGED BY:

CONFIDENTIAL AND PROPRIETARY INFORMATION.
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY
INFORMATION OF ROCKWELL AUTOMATION, INC. AND MAY
NOT BE USED, COPIED OR DISCLOSED TO OTHERS, EXCEPT
WITH THE AUTHORIZED WRITTEN PERMISSION OF ROCKWELL
AUTOMATION, INC.

DATE:2021-08-16	SHEET 2 OF 2
SIZE D1R	VER
D 10006321536	00