

Circuit Protection Design and SCCR Tables-Servo Drives

Product Family	Protective Device	50Hz Voltages								60Hz Voltages							
		Single Phase Inputs		3 Phase Inputs						Single Phase Inputs		3 Phase Inputs					
		110V	220V	220-230V	380-400V	415V	440V	500V	525V	120V	230V	200-208V	230-240V	300V	480V	600V	690V
Kinetix 300/350 Single-Axis EtherNet/IP	140M Motor Protection Circuit Breakers	SCCR-6103M.pdf		SCCR-6143M.pdf	SCCR-6163M.pdf	SCCR-6173M.pdf	SCCR-6183M.pdf			SCCR-6117M.pdf			SCCR-6157M.pdf				
	IEC DIN Class Fuses	SCCR-6101M.pdf		SCCR-6141M.pdf	SCCR-6161M.pdf	SCCR-6171M.pdf	SCCR-6181M.pdf										
	UL Class J Fuses									SCCR-6115M.pdf			SCCR-6155M.pdf				
Kinetix 5500	140UT-D & G Frame Size			SCCR-6242M.pdf	SCCR-6262M.pdf										SCCR-6296M.pdf		
	Standard Fuse Selection for Component Sizing																
	140UT-D & G Frame Size					SCCR-6271M.pdf	SCCR-6281M.pdf			SCCR-6235M.pdf			SCCR-6255M.pdf				
Kinetix 5700	UL/CSA Class CC or J Input Line Fuses				SCCR-6361E.pdf	SCCR-6371E.pdf	SCCR-6381E.pdf									SCCR-6395E.pdf	
	140MT Motor Protection Circuit Breakers				SCCR-6363E.pdf	SCCR-6373E.pdf	SCCR-6383E.pdf									SCCR-6397E.pdf	
	1489 Miniature Circuit Breaker				SCCR-6365E.pdf	SCCR-6375E.pdf	SCCR-6385E.pdf									SCCR-6398E.pdf	
	140G Moded Case Circuit Breaker				SCCR-6367E.pdf	SCCR-6377E.pdf	SCCR-6387E.pdf									SCCR-6396E.pdf	
Kinetix 6000	UL/CSA Class CC or J Input Line Fuses, 140M F Frame Size, 1489M 3-Pole, 140G Frame Size			SCCR-6420M.pdf	SCCR-6460M.pdf	SCCR-6479M.pdf	SCCR-6485M.pdf						SCCR-6455M.pdf		SCCR-6495M.pdf		