

Specs table for ASEM 6300MA

6300MA		
	Mounting	VESA 75 or 100
	Branding	A-B Branding
	Handles	With vertical side handles
	Protection Grade	IP65
	Operating Temperature	0° C ... 50° C (32° F ... 122° F)
	Storage Temperature	-5° C ... 60° C (14° F ... 140° F)
	Humidity	20% ... 90% RH (non-condensing)
Family Configurable Functions for 6300MA	Video input	1x DVI-D and 1x DisplayPort or Remote Video Link (RVL)
	Screen sizes & Resolutions – Landscape	15.6", 18.5", 21.5", 24" (16:9 1920x1080)
	Screen sizes & Resolutions – Portrait	21.5", 24" (9:16 1080x1920)
	Bezel and Touch	Aluminum with Resistive Single Touch, Aluminum & Glass TrueFlat with Capacitive Multitouch (PCAP)
	Power	24 VDC isolated, no UPS
	Remote Video Link (RVL)	With or without optional RVL
	Handles	Additional configurations will be available soon. Perimeter handles can also be purchased as accessories
	Configurable Button Area	15.6" Landscape: Space for 9 devices 18.5" Landscape: Space for 11 devices 21.5" or 24" Landscape: Space for 13 devices 21" Portrait: Space for 7 devices 24" Portrait: Space for 8 devices Or no button area