

CONFIDENTIAL - PROPRIETARY										*THIS DRAWING AND SPECIFICATION, HEREIN, ARE THE PROPERTY OF ASEM SpA AND MUST NOT BE REPRODUCED OR COPIED OR USED IN WHOLE OR IN PART AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION*									
COMMON TOLERANCE	QUALITY	<6	>6 ≤30	>30 ≤120	>120 ≤315	>315 ≤1000	>1000 ≤4000	>4000	SHORT SIDE	NOTE:				>120					
										- ACCURATE TRIM REQUESTED									
	COARSE	0.2	0.5	0.8	1.2	2	3	4	5	ANGULAR COMMON TOLERANCE	- BENDING RADIUS: MINIMUM POSSIBLE				>30 ≤120				
											- PERPENDICULAR AND PARALLEL GEOMETRIC TOLERANCE: MEDIUM (Max 0.3 mm) ON ALL DIRECTIONS								
	MEDIUM	0.1	0.2	0.3	0.5	0.8	1.2	2	3	1 ±	- THE DIMENSIONS INCLUDING THE TREATMENT				'30'				
	ACCURATE	0.05	0.1	0.15	0.2	0.3	0.5								'20'				

CONFIDENTIAL - PROPRIETARY

THIS DRAWING AND SPECIFICATION, HEREIN, ARE THE PROPERTY OF ASEM SpA AND MUST NOT BE REPRODUCED OR COPIED OR USED IN WHOLE OR IN PART AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION





NOTE: - ACCURATE TRIM REQUESTED - BENDING RADIUS: MINIMUM POSSIBLE - PERPENDICULAR AND PARALLEL GEOMETRIC TOLERANCE: MEDIUM (Max 0.3 mm) ON ALL DIRECTIONS - THE DIMENSIONS INCLUDING THE TREATMENT		ALL DIMENSIONS IN mm (INCHES)	
SHORT SIDE		ANGULAR COMMON TOLERANCE	
>120		10°	
>30 <120		20°	
>6 <30		30°	
>3 <6		1.2	

QUALITY	<6		>4000									
	>6 <30		>30 <120		>120 <315		>315 <1000		>1000 <2000		>2000 <4000	
	COARSE		0.2		0.5		0.8		1.2		2	
	MEDIUM		0.1		0.2		0.3		0.5		1	
	ACCURATE		0.05		0.1		0.15		0.2		0.3	




"THIS DRAWING AND SPECIFICATION, HEREIN, ARE THE PROPERTY OF ASEM SPA AND MUST NOT BE REPRODUCED OR COPIED OR USED IN WHOLE OR IN PART AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION"


B	
C	
$\trianglelefteq$	
D	

E	F
---	---



DETTAGLIO A



MATERIAL					THICKNESS mm	MODIFICATION N°		DATE	
TREATMENT								SIGNATURE	
			1st DRAW	DESIGN	CHECKED	TOLERANCE MEDIUM		SCALE 1:5	
		DATE	08/06/2022			NOT QUOTED BEVELS 2x45°	UNIT mm	SHEET 9 of 9	
		SIGNATURE	Dereani			NOT QUOTED RADIUS R2			
TITLE DIMA VK3500 / MK200 15,6 TOP ARM RESISTIVO CON MANIGLIE E VASSOIO PORTA TASTIERA									
DRAWING N° 00_d18201907						RELEASE A		LEVEL 00	SIZE A3