








CONFIDENTIAL-PROPRIETARY

THIS DRAWING AND SPECIFICATIONS, HEREIN, ARE THE PROPERTY OF ASEM SpA AND MUST NOT BE REPRODUCED OR COPIED OR USED IN WHOLE OR IN PART AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION.

SHORT SIDE	>3 ≤6	>6 ≤30	>30 ≤120	>120
ANGULAR COMMON TOLERANCE	±1°	±30'	±20'	±10'

QUALITY	<6	>6 ≤30	>30 ≤120	>120 ≤315	>315 ≤1000	>1000 ≤2000	>2000 ≤4000	>4000
COMMON TOLERANCE	COARSE	±0.2	±0.5	±0.8	±1.2	±2	±3	±5
	MEDIUM	±0.1	±0.2	±0.3	±0.5	±0.8	±1.2	±2
	ACCURATE	±0.05	±0.1	±0.15	±0.2	±0.3	±0.5	±3



NOT QUOTED BEVELS	/	MATERIAL	/	TREATMENT	/
-------------------	---	----------	---	-----------	---

MOD. N°		DATE		REPLACES		DATE	
SIGNATURE				REPLACED BY		DATE	
						SIGN.	

1st DRAW	DESIGN	CHECKED	TOLERANCE	SCALE	UNIT	SHEET
25.08.21	25.08.21		MEDIUM	/	MM	1 OF 3








TITLE	DIMA VK3500 21.5" BOTTOM ARM	RELEASE	A	LEVEL	00
DRAWING N°	DIMA_VK3500_215_BOTTOM				

CONFIDENTIAL—PROPRIETARY

"THIS DRAWING AND SPECIFICATIONS, HEREIN, ARE THE PROPERTY OF ASEM SpA AND MUST NOT BE REPRODUCED OR COPIED OR USED IN WHOLE OR IN PART AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION."

SHORT SIDE	>3 ≤6	>6 ≤30	>30 ≤120	>120
ANGULAR COMMON TOLERANCE	±1°	±30'	±20'	±10'

QUALITY	<6	>6 ≤30	>30 ≤120	>120 ≤315	>315 ≤1000	>1000 ≤2000	>2000 ≤4000	>4000
COARSE	±0.2	±0.5	±0.8	±1.2	±2	±3	±4	±5
MEDIUM	±0.1	±0.2	±0.3	±0.5	±0.8	±1.2	±2	±3
ACCURATE	±0.05	±0.1	±0.15	±0.2	±0.3	±0.5		



NOT QUOTED BEVELS /	MATERIAL /	TREATMENT /
------------------------	---------------	----------------

[illegible]

		Industry Informatica	
SIGNATURE		TOLERANCE	
1st DRAW	DESIGN	CHECKED	
DATE	25.08.21	25.08.21	
ROMANO	ROMANO		
		MEDIUM	
UNIT	SHEET	OF	
MM	2	3	






TITLE DIMA VK3500 21.5" BOTTOM ARM	
DRAWING N° DIMA_VK3500_215_BOTTOM	RELEASE A LEVEL 00

CONFIDENTIAL-PROPRIETARY

THIS DRAWING AND SPECIFICATIONS, HEREIN, ARE THE PROPERTY OF ASEM SpA AND MUST NOT BE REPRODUCED OR COPIED OR USED IN WHOLE OR IN PART AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION.

SHORT SIDE	>3 ≤6	>6 ≤30	>30 ≤120	>120
ANGULAR COMMON TOLERANCE	±1°	±30'	±20'	±10'

QUALITY	<6	>6 ≤30	>30 ≤120	>120 ≤315	>315 ≤1000	>1000 ≤2000	>2000 ≤4000	>4000
COMMON TOLERANCE	COARSE	±0.2	±0.5	±0.8	±1.2	±2	±3	±4
	MEDIUM	±0.1	±0.2	±0.3	±0.5	±0.8	±1.2	±2
	ACCURATE	±0.05	±0.1	±0.15	±0.2	±0.3	±0.5	



NOT QUOTED BEVELS		MATERIAL		TREATMENT	
/		/		/	
MOD. N°		DATE		REPLACES	
SIGNATURE		DATE		REPLACED BY	
1st DRAW		DATE	25.08.21	DESIGN	ROMANO
CHECKED		DATE	25.08.21	DESIGN	ROMANO
TOLERANCE		MEDIUM		SCALE	
/		/		UNIT	
/		/		MM	
/		/		SHEET	
/		/		OF	
/		/		3	
/		/		3	

TITLE		DIMA VK3500 21.5" BOTTOM ARM	
DRAWING N°		DIMA_VK3500_215_BOTTOM	
RELEASE		A	
LEVEL		00	