








CONFIDENTIAL-PROPRIETARY

THIS DRAWING AND SPECIFICATIONS, HEREIN, ARE THE PROPERTY OF ASEMI SpA AND MUST NOT BE REPRODUCED OR COPIED OR USED IN WHOLE OR IN PART AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION.

SHORT SIDE	>3 ≤6	>6 ≤30	>30 ≤120	>120
ANGULAR COMMON TOLERANCE	±1°	±30'	±20'	±10'

QUALITY	<6	>6 ≤30	>30 ≤120	>120 ≤315	>315 ≤1000	>1000 ≤2000	>2000 ≤4000	>4000
COMMON TOLERANCE	COARSE	±0.2	±0.5	±0.8	±1.2	±2	±3	±4
	MEDIUM	±0.1	±0.2	±0.3	±0.5	±0.8	±1.2	±2
	ACCURATE	±0.05	±0.1	±0.15	±0.2	±0.3	±0.5	



NOT QUOTED BEVELS	/	MATERIAL	/	TREATMENT	/
-------------------	---	----------	---	-----------	---

MOD. N°	DATE	SIGNATURE	1st DRAW	DESIGN	CHECKED	REPLACES	REPLACED BY	DATE	SIGNATURE

ASEMI	Industria Informatica	SIGNATURE	DATE	25.08.21	ROMANO	DESIGN	25.08.21	CHECKED	ROMANO	TOLERANCE	MEDIUM	SCALE	/	UNIT	MM	SHEET	1	OF	3
-------	-----------------------	-----------	------	----------	--------	--------	----------	---------	--------	-----------	--------	-------	---	------	----	-------	---	----	---








TITLE	DIMA VK3500 21.5" VESA	RELEASE	A	LEVEL	00
DRAWING N°	DIMA_VK3500_215_VESA				

CONFIDENTIAL-PROPRIETARY

THIS DRAWING AND SPECIFICATIONS, HEREIN, ARE THE PROPERTY OF ASEM SpA AND MUST NOT BE REPRODUCED OR COPIED OR USED IN WHOLE OR IN PART AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION.

SHORT SIDE	>3 ≤6	>6 ≤30	>30 ≤120	>120
ANGULAR COMMON TOLERANCE	±1°	±30'	±20'	±10'

QUALITY	<6	>6 ≤30	>30 ≤120	>120 ≤315	>315 ≤1000	>1000 ≤2000	>2000 ≤4000	>4000
COMMON	COARSE	±0.2	±0.5	±0.8	±1.2	±2	±3	±4
TOLERANCE	MEDIUM	±0.1	±0.2	±0.3	±0.5	±0.8	±1.2	±2
	ACCURATE	±0.05	±0.1	±0.15	±0.2	±0.3	±0.5	



NOT QUOTED BEVELS	MATERIAL	TREATMENT
/	/	/

MOD. N°	DATE	SIGN.	REPLACES	DATE	SIGN.
SIGNATURE			REPLACED BY		SIGN.

DATE	1st DRAW	DESIGN	CHECKED	TOLERANCE	SCALE	UNIT	SHEET
SIGNATURE	25.08.21	25.08.21		MEDIUM	/	MM	2 OF 3





TITLE	DIMA VK3500 21.5" VESA	RELEASE	A	LEVEL	00
DRAWING N°	DIMA_VK3500_215_VESA				

CONFIDENTIAL—PROPRIETARY

"THIS DRAWING AND SPECIFICATIONS, HEREIN, ARE THE PROPERTY OF ASEM SpA AND MUST NOT BE REPRODUCED OR COPIED OR USED IN WHOLE OR IN PART AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION."

SHORT SIDE	>3 ≤6	>6 ≤30	>30 ≤120	>120
ANGULAR COMMON TOLERANCE	±1°	±30'	±20'	±10'

QUALITY	<6	>6 ≤30	>30 ≤120	>120 ≤315	>315 ≤1000	>1000 ≤2000	>2000 ≤4000	>4000
COARSE	±0.2	±0.5	±0.8	±1.2	±2	±3	±4	±5
MEDIUM	±0.1	±0.2	±0.3	±0.5	±0.8	±1.2	±2	±3
ACCURATE	±0.05	±0.1	±0.15	±0.2	±0.3	±0.5		



NOT QUOTED BEVELS						MATERIAL		TREATMENT		
MODIFICATION								DATE		
MOD. N°								SIGN.		
DATE								DATE		
SIGNATURE								SIGN.		
 Industria Informatica								REPLACES		
								BY		
								TOLERANCE		
								MEDIUM		
SIGNATURE		1st DRAW	DESIGN	CHECKED	SCALE / 					
DATE		25.08.21	25.08.21							
ROMANO		ROMANO	ROMANO		UNIT MM SHEET 3 OF 3					